



FEATURES:

- Enables interconnection between telephone equipment and BNC based test instruments.
- Readily adapts standard phone jacks for BNC Cables.
- BNC (Female) contact is gold plated Beryllium Copper for noise free connection.
- Adapter is tarnish resistant for good lab appearance.

MATERIALS:

BNC (Male): Body – Brass, Tarnish Resistant

Center Contact: Beryllium Copper, Gold Plated

Dielectric: PTFE

Handle: Brass, Nickel Plated

Phone Plug (Two Conductors): Brass, Nickel Plated

RATINGS:

Operating Voltages: 500 VRMS

Operating Temperature: +125°C (+257°F)

Impedance: 50 Ohms

All dimensions are in inches. Tolerances (except noted): .xx = $\pm .02"$ (.51 mm), .xxx = $\pm .005"$ (.127 mm).

All specifications are to the latest revisions. Specifications are subject to change without notice.

Registered trademarks are the property of their respective companies. Made in USA

Pomona®

**Model 1297
BNC (Female) To Standard 1/4"
Two Conductor Phone Plug**

ORDERING INFORMATION: Model 1297

All dimensions are in inches. Tolerances (except noted): .xx = $\pm .02"$ (.51 mm), .xxx = $\pm .005"$ (.127 mm).

All specifications are to the latest revisions. Specifications are subject to change without notice.

Registered trademarks are the property of their respective companies. Made in USA

6/9/99

SY/EH/LS

S:\Engineering\Release\Datasheets\FlukeDataSheet\d1297_1_01.doc

**Sales: 800-490-2361 Fax: 888-403-3360
Technical Assistance: 800-241-2060**

PomonaACCESS 90502 (800) 444-6785 or (425) 446-6010
More drawings available at www.pomonaelectronics.com

Page 1 of 2