





RG59/U

205-000BK	1' Black – Nickel
205-005BK	2' Black – Nickel
205-010□□	3' Black, White – Nickel
205-015□□	6' Black, White – Nickel
205-018BK	9' Black – Nickel
205-020□□	12' Black, White – Nickel
205-030□□	25' Black, White – Nickel
205-035□□	50' Black, White – Nickel
205-040□□	75' Black, White – Nickel
205-045□□	100' Black, White – Nickel
205-210BK	3' Black – Gold
205-215BK	6' Black – Gold
205-218BK	9' Black – Gold
205-220BK	12' Black – Gold
205-225BK	18' Black – Gold
205-230BK	25' Black – Gold
205-233BK	35' Black – Gold
205-235BK	50' Black – Gold
205-240BK	75' Black – Gold
205-245BK	100' Black – Gold

F Coaxial Cables


Suitable for General Video Applications
75Ω Low-Loss RG59/U Coaxial Cables
Molded Nickel or Gold-Plated F Connectors
AWG22 Solid Copper/CCS Center Conductor
100% Aluminum Foil Shield
32x0.12mm Copper/Aluminum Braid

205-000BK	1' Black RG59 F-F Cable
205-005BK	2' Black RG59 F-F Cable
205-010BK	3' Black RG59 F-F Cable
205-010WH	3' White RG59 F-F Cable
205-015BK	6' Black RG59 F-F Cable
205-015WH	6' White RG59 F-F Cable
205-018BK	9' Black RG59 F-F Cable
205-020BK	12' Black RG59 F-F Cable
205-020WH	12' White RG59 F-F Cable
205-030BK	25' Black RG59 F-F Cable
205-030WH	25' White RG59 F-F Cable
205-035BK	50' Black RG59 F-F Cable
205-035WH	50' White RG59 F-F Cable
205-040BK	75' Black RG59 F-F Cable
205-040WH	75' White RG59 F-F Cable
205-045BK	100' Black RG59 F-F Cable
205-045WH	100' White RG59 F-F Cable
205-210BK	3' Black RG59 F-F Gold Cable
205-215BK	6' Black RG59 F-F Gold Cable
205-218BK	9' Black RG59 F-F Gold Cable
205-220BK	12' Black RG59 F-F Gold Cable
NEW ► 205-225BK	18' Black RG59 F-F Gold Cable
NEW ► 205-230BK	25' Black RG59 F-F Gold Cable
NEW ► 205-233BK	35' Black RG59 F-F Gold Cable
NEW ► 205-235BK	50' Black RG59 F-F Gold Cable
NEW ► 205-240BK	75' Black RG59 F-F Gold Cable
NEW ► 205-245BK	100' Black RG59 F-F Gold Cable



RG59/U

205-110BK	3' Black – Nickel
205-115BK	6' Black – Nickel
205-120BK	12' Black – Nickel
205-310BK	3' Black – Gold
205-315BK	6' Black – Gold



75Ω Ultra-Thin

210-003GY	3' Mini-Coax Gold
210-006GY	6' Mini-Coax Gold
210-012GY	12' Mini-Coax Gold
210-025GY	25' Mini-Coax Gold

F-Quick Coaxial Cables

Suitable for General Video Applications
75Ω Low-Loss RG59/U Coaxial Cables
Fully Molded F-Quick Connectors with
Compression Ring and Fixed Center Pin
Nickel or Gold-Plated Connectors
AWG22 Solid Copper/CCS Center Conductor
100% Aluminum Foil Shield
32x0.12mm Copper/Aluminum Braid

205-110BK	3' Black F-F Quick Cable
205-115BK	6' Black F-F Quick Cable
205-120BK	12' Black F-F Quick Cable
205-310BK	3' Black F-F Quick Cable Gold
205-315BK	6' Black F-F Quick Cable Gold

F Mini-Coax Python™ Jumpers

75Ω Ultra-Thin High-Definition F Cables
AWG27 Solid Bare-Copper Center Conductor
Low-Loss Low-Noise – Double High-Density Shield
100% 0.06mm Aluminum-Polyester Foil Shield
95% Coverage 64x0.10mm Tinned-Copper Braid
0.118" OD Grey Ultra-Flex PVC Jacket
High-Reliability Brass Gold-Plated F Connectors
Fully Molded Construction

210-003GY	3' F-F Mini-Coax Python Gold
210-006GY	6' F-F Mini-Coax Python Gold
210-012GY	12' F-F Mini-Coax Python Gold
210-025GY	25' F-F Mini-Coax Python Gold