



Features:

- * 5mm Lamp LED
- * Emitting Color Red Green Blue
- * Low Power Consumption
- * Ideal For Backlight Toy Light-Gift Indicator

Circuit and Package Dimension

Absolute Maximum Rating

Item	Symbol	Absolute Maximum Rating	Unit
Forward Current	I_F	20	mA
Peak Forward Current*	I_{FP}	100	mA
Reverse Voltage	V_R	5	V
Reverse Current	I_R	10	uA
Power Dissipation	P_D	150	mW
Electrostatic discharge	E_{SD}	800	V
Operation Temperature	T_{OPR}	-25~+80	°C
Storage Temperature	T_{STG}	-5~+45	°C
Lead Soldering Temperature	T_{SOL}	Max.260°C for 5sec Max(3mm from the base of the epoxy bulb)	

Typical Optical/Electrical Characteristics

Product Type	Lens Color	Emitting Color	Forward Voltage(v)		Prpc Wavelength (nm)		Luminous Intensity(mcd)		50% Power Angle(deg)
			Type	Max.	Type.	Max.	Min.	Type	Type
5TSRGB-A/C	Water Clear	R	1.80	2.40	630	640	3000	4000	18
		G	3.20	3.60	515	525	4000	6000	
		B	3.20	3.60	460	470	900	1000	
5WSRGB-A/C	Diffused	R	1.80	2.40	630	640	2000	3000	45
		G	3.20	3.60	515	525	3000	5000	
		B	3.20	3.60	460	470	700	900	