



**Order symbol:** PC 30/25-C3  
**Product nbr:** 7520031  
**Description:** Enclosure, PC  
**Remarks:** With aluminium front plate

**EAN:** 6418074005854  
**El. number:** Finland: 3420830

Including: Base, terminal compartment cover with EPDM gasket and screws for mounting plate/DIN-rail. -3 and -L3 versions: Transparent cover with PUR gasket, hinges, locking devices; FC version: Closed PC frame front plate with PUR gasket and cover screws.

Sample photo

| Dimensions:      |  | Length                  | Width | Height | Rating:                                      |
|------------------|--|-------------------------|-------|--------|----------------------------------------------|
| mm:              |  | 314                     | 260   | 95     | Ingress Protection (EN 60529): IP 65         |
| inch:            |  | 12.4                    | 10.2  | 3.7    | Impact Resistance (EN 62262): IK 08/07       |
| Materials:       |  |                         |       |        | Electrical insulation: Totally insulated     |
| Material:        |  | Polycarbonate           |       |        | Halogen free (DIN/VDE 0472, Part 815): Yes   |
| Base colour:     |  | RAL 7035                |       |        | UV resistance: UL 508                        |
| Gasket material: |  | EPDM                    |       |        | Flammability Rating (UL 746 C 5): UL 746C 5V |
| Temperatures:    |  |                         |       |        | Glow Wire Test (IEC 695-2-1) °C: 960         |
| Short term:      |  | -40 ... 120 °C          |       |        | NEMA Class: NEMA 1, 3, 3R, 12, 13            |
| Continuous:      |  | -40 ... 80 °C           |       |        | Certificates:                                |
| Short term:      |  | -40 ... 250 °F          |       |        | Underwriters Laboratories                    |
| Continuous:      |  | -40 ... 175 °F          |       |        | Fimko                                        |
| Accessories:     |  |                         |       |        | Europe EN 62208: 2003                        |
| MP 30/25         |  | Mounting plate          |       |        | UL Canada                                    |
| FP 30/25         |  | Front plate (aluminium) |       |        | Gost R                                       |
| FC PC 30/25      |  | Frame of PC front plate |       |        |                                              |

