




Ind. a - Revision : 11-2008

2RREu35 225x63R P/N C25-A4

Voltage	Frequency	Input power	Current	Capacitor	Airflow	Speed rotation	Noise level	Rotation direction	Operating temperature
V	Hz	Wa	A	µF	m³/h	RPM	dBA		Min / Max
230	50	150	0,66	4,0	1 235	2 480	67	R	-40°C / +70°C
230	60	197	0,86	4,0	1 315	2 580	69	R	-40°C / +60°C
230	50				726 CFM				-40°F / +158°F
230	60				774 CFM				-40°F / +140°F



- Weight : 2,4 Kg
- Ball bearing
- Class F, thermally protected
- IP44 protection
- G2.5 balancing
- Rotor : black paint
- PA 6/6 UL 94 V-0 plastic impeller
- UL approved motor

UL2111 (XEWR2,8)
N° File E135223
2RS935




Capacitor for 50Hz 19220

Capacitor for 60Hz 19220

Finger guard 21194

Inlet cone 16214



Non contractual document. All specifications are subject to change without prior notice. Picture for information only.