


300W Single Output, Convection Cooled Power Supplies

Features

- ◆ Universal Input (85 - 265VAC)
- ◆ Power Factor Corrected
- ◆ Convection cooling
- ◆ Five year warranty
- ◆ Less than 0.5mA earth leakage current



Key Market Segments & Applications



Specifications

Model		ZWS300BAF
Input Voltage	V	85-265VAC (47-63Hz), 120-370VDC
Input Current	A	3.5 / 1.8
Inrush Current ⁽¹⁾⁽²⁾	A	15 / 30
Power Factor	-	0.98 at 100VAC, 0.93 at 200VAC, Meets EN61000-3-2
Leakage Current	mA	0.5mA Max. Typically 0.2mA (100VAC), 0.4mA (230VAC)
Temperature Coefficient	%/°C	<0.02%/°C
Overcurrent Protection ⁽³⁾	-	>116% of rated output current
Overvoltage Protection	V	24V: 28.8-33.6V, 36V: 41.4-48.6V, 48V: 55.2-64.8V
Hold Up Time (Typ) ⁽¹⁾	ms	18ms at 100VAC input
Efficiency ⁽¹⁾	%	88 / 91%
Remote On/Off	-	Optional, contact factory
Operating Temperature	°C	-10°C to +70°C, derate linearly to 40% load from 45°C to 70°C
Storage Temperature	°C	-30 to +75°C
Humidity (non condensing)	%RH	Operating: 30 - 90%RH, Storage: 10 - 90%RH
Cooling	-	Convection
Withstand Voltage	-	Input to Ground 2kVAC (20mA), Input to Output 3kVAC (20mA), Output to Ground 500VAC (20mA) for 1 min.
Isolation Resistance	-	>100M at 25°C & 70%RH, Output to Ground 500VDC
Vibration (non operating)	-	10 - 55Hz (1 minute sweep), 19.6m/s ² constant X, Y, Z 1 hour each
Shock	-	< 196.1 m/s ²
Safety Agency Certifications	-	UL60950-1, CSA60950-1, EN60950-1, EN50178 OV II, CE Mark
Conducted & Radiated EMI	-	EN55011/EN55022-B, FCC Class B, VCCI-B
Immunity	-	EN61000-4-2 (lvl2, 3), -3 (lvl 3), -4 (lvl 3), -5 (lvl 3, 4), -6 (lvl 3), -8 (lvl 4), -11; EN61000-6-2
Weight (Typ)	g	540g
Size (WxHxD)	in (mm)	3.31 x 1.65 x 7.09" (84 x 42 x 180)
Warranty	yrs	Five Years

Notes:

(1) 100 / 200VAC Input


(2) 25°C ambient (cold start)

(3) Avoid prolonged operation in overload

Model Selector

Model	Output Voltage	Adjustment Range	Max Current	Max Power	Line Reg (mV)	Load Reg (mV)	Ripple & Noise (mV)
ZWS300BAF24	24V	21.6 - 27.5V	12.5A	300W	96	150	150
ZWS300BAF36	36V	32.4 - 39.6V	8.4A	302.4W	144	240	250
ZWS300BAF48	48V	39.5 - 52.8V	6.3A	302.4W	192	240	250

Outline Drawing



Similar Products

ZWS-B, -BAF, -BP	10W to 240W Single output
HWS	15W to 1800W Single Output, Enclosed
EFE	300W to 400W Single Output, Medical & ITE
CFE400M	300W to 400W Single Output, Medical & ITE

Options

Suffix	Description
-	JST Connectors
/L	L Bracket
/A	Cover & L Bracket
/R	Remote On/Off
/T	Screw Terminals
/CO2	PCB Coating
Example	ZWS300BAF24/TL

For Additional Information, please visit
us.tdk-lambda.com/lp/products/zws-series.htm

