

THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION ,19 .
© COPYRIGHT 19 BY AMP INCORPORATED. ALL INTERNATIONAL RIGHTS RESERVED.

LOC DIST
G 14

P F

ZONE LTR

DESCRIPTION
D EC 0720-0279-93

REVISIONS
DATE APPD
6-23-93 \$56 BB

AMP

WIRE RANGE


4 HD AWG

STRANDED

METRIC

DIMENSIONS LISTED IN mm [INCHES]

1. TONGUE MATERIAL THK 2.31±0.08[.091±.004]
FOR 11.25[.443] MAX WIRE INS DIA



AMP INCORPORATED
CUSTOMER SERVICE SYSTEMS

MAX RECOMMENDED OPERATING
TEMPERATURE:
105°C

VOLTAGE RATING:
-

CIRCULAR MIL AREA:
16.8-26.7mm² [33,100-52,600]
STRANDED

FINISH
TIN PLATE PER MIL-T-10727

FOR ADDITIONAL
PRODUCT INFORMATION OR
COPIES OF DRAWINGS
AND TECHNICAL DOCUMENTS
1-800-522-6752
FOR APPLICATION
TOOLING ASSISTANCE CENTER
1-800-722-1111
FOR ORDER ENTRY
1-800-526-5142

THIS DRAWING IS A CONTROLLED DOCUMENT FOR
AMP INCORPORATED. IT IS SUBJECT TO CHANGE
AND THE CONTROLLING ENGINEERING ORGANIZATION
SHOULD BE CONTACTED FOR THE LATEST REVISION.

3/8	9.91±0.13 [.390±.005]	-	LOOSE PC	1-331421-1
5/16	8.33±0.13 [.328±.005]	-		1-331421-0

DO NOT SCALE PRINT. UNLESS SPECIFIED DIMENSIONS IN mm [INCHES] TOLERANCES ON: 2 PLC DEC ± 0.20[.008] 3 PLC DEC ± - ANGLES	OR 6-21-93 S.S. SOULDEN CHK 6-21-93 R. HERSEY APPD 6-21-93 B. BARE	QTY
MATERIAL COPPER PER ASTM B-152 NYLON (MIL-M-20693) TYPE 1 COLOR: YELLOW	NAME AMP AMP Incorporated Harrisburg, PA 17105-3608	PACKAGE TYPE
FINISH TIN PLATE PER MIL-T-10727	TERMINAL, RING TONGUE, TERMINYL WIRE SIZE: 4 HD AWG	PART NO

SIZE B	CAGE CODE 00779	DRAWING NO G-331421
WEIGHT -	SCALE NTS	SHEET 1 OF 1