

Terminals

Vinyl Insulated Ring Terminals



- Molded Funnel Entry Insulator
- Brazed Seam
- Internal Barrel Serrations

Dimensional Images

Dimension Information In F.P.S (U.S)

[Display in metric standards \(C.G.S\)](#)

Catalog No	Wire Range	Bolt Size D2#	Bolt Size D2 (In.)	Dim. W (In.)	Dim. F (In.)	Dim. L (In.)	Dim. E (In.)	Dim. D (In.)	Dim. d1 (In.)	Dim. T (In.)
KV14-8R-M	16-14 A. W.G. 1.5-2.5 sq. mm	#8	0.169	0.260	0.248	0.803	0.433	0.177	0.091	0.031

For Mylar Tape replace box quantity with (T). Example: KV18-6R-T
 Maximum Electrical Rating: 105°C 600 Volts Max.
 Terminal Material: Copper

Tools Used

Packaging Information

Catalog#	Unit Quantity	Standard Quantity Package	Weight (lbs.)	Weight UOM
KV14-8R-M	1000	20000	2.100	Per 1000

[Smart Search Results](#) [View Product Category](#)

[Print](#)
[Back](#)