

5








4

3

2

1

1:1



Steckgesicht n.
Contact face acc.
IEC 61076-2-101

Leiterquerschnitt conductor cross section	0,34 - 0,75mm ² AWG22-AWG18
Kabeldurchmesser cable outside diameter	6,0-8,0mm

 All Dimensions in mm Original Size DIN A 4			Techn. Character.			Maßstab/Scale 2:1
Mod.	Dat.	Name		Dat.	Name	
EC01896	18.05.10	DY	Detail.	13.02.03	Ste	
412800	19.03.07	DY	Insp.		SR	
411606	08.08.05	DY	Stand.			
410925	10.03.04	DY	HARTING Electronics GmbH & Co. KG D-32339 ESPELKAMP			
410369						

Nicht tolerierte Maße/ Free size tolerances	
Rundsteckverbinder/ Circular connector M12-L 3polig Buchse/M12-L 3poles female bleifrei/lead free	
TB 21 03 212 2306	Blatt/ page /
Sub.	