

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [43335-2003](#)

**Status:** **Active**

**Overview:** Flat Blade


**Description:** 7.50mm Pitch, Flat Blade Appliance Receptacle Housing, Single Row, 3 Circuits, Nylon PA66, UL 94V-0, Natural with TPA, Glow Wire Compatible

**Documents:**

[3D Model](#)  
[Drawing \(PDF\)](#)

[Product Specification PSX-43335-9999 \(PDF\)](#)

[Packaging Specification PK-43335-001 \(PDF\)](#)  
[RoHS Certificate of Compliance \(PDF\)](#)



*Series*

*image - Reference only*

**Agency Certification**

CSA  
UL

**General**

Product Family  
Series  
Application  
Comments

LR19980  
E29179

Crimp Housings

43335

Power, Wire-to-Wire

This Molex product is manufactured from material that has the following ratings, tested by independent agencies :. a) A Glow Wire Ignition Temperature (GWIT) of at least 775 deg C per IEC 60695-2-13.. b) A Glow Wire Flammability Index (GWFI) above 850 deg C per IEC 60695-2-12.and hence complies with the requirements set out in the International Standard IEC 60335-1 5th edition - household and similar electrical appliances - safety; section 30 Resistance to heat and fire.<P><P>The customers using this product must determine its suitability for use in their particular application through testing or other acceptable means as described in end-product glow-wire flammability test standard IEC 60695-2-11 and any applicable product end-use standard(s).<P>If it is determined during the customer's evaluation of suitability, that higher performance is required, please contact Molex for possible product options.

[Flat Blade](#)

Flat Blade

822348665631

Overview  
Product Name  
UPC

**Physical**

Breakaway  
Circuits (maximum)  
Color - Resin  
Flammability  
Gender  
Glow-Wire Compliant  
Keying to Mating Part  
Lock to Mating Part  
Material - Resin  
Net Weight  
Number of Rows  
Packaging Type  
Panel Mount  
Pitch - Mating Interface

No  
3  
Black  
94V-0  
Receptacle  
Yes  
None  
Yes  
Nylon  
2.343/g  
1  
Bag  
No  
7.50mm

**EU RoHS**

**ELV and RoHS**

**Compliant**

**REACH SVHC**

**Contains SVHC: No**  
**Low-Halogen Status**

**Low-Halogen**

**China RoHS**



**Need more information on product environmental compliance?**

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)  
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

**Search Parts in this Series**

[43335Series](#)

**Mates With**

[43180 Flat Blade Plug Housing](#)

**Use With**

[43375 Female Terminals](#)

Pitch - Termination Interface 7.50mm  
Polarized to Mating Part Yes  
Ports 1  
Stackable No  
Temperature Range - Operating -40°C to +75°C

**Material Info**

Old Part Number 43352003

**Reference - Drawing Numbers**

Packaging Specification PK-43335-001  
Product Specification PSX-43335-9999  
Sales Drawing SD-43335-\*003

This document was generated on 08/08/2014

**PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION**

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex](#):

[43335-2003](#)