



English | 简体中文 | 日本語

Search Entire Site

GO

Contact IDT | Investors | Press

About IDT

Products

Applications

Support

myIDT

Document Search | Package Search | Parametric Search | Cross Reference Search | Green & RoHS | Calculators | Thermal Data | Reliability & Quality | Military

Home > Products > Clock / Timing Devices > PC-Notebook-Server Clocks > Clock Synthesizer by Chipset Vendor > Desktop Chipsets > 9LP505-2 > 9LP505-2HFLF

Add to myIDT [?]

You may also like...

9LP505-2HFLF

Category: Desktop Chipsets
Generic Part: 9LP505-2
Market Group: PC CLOCK
Description: PC MAIN CLOCK
CK505 clock, 56-pin Intel Yellow Cover part

Output Features:

- 2 - CPU differential low power push-pull pairs
- 7 - SRC differential low power push-pull pairs
- 1 - CPU/SRC selectable differential low power push-pull pair
- 1 - SRC/DOT selectable differential low power push-pull pair
- 5 - PCI, 33MHz
- 1 - PCI_F, 33MHz free running
- 1 - USB, 48MHz
- 1 - REF, 14.318MHz

Time is money

Parameters

Package	SSOP 56 (PVG56)
Voltage	2.5/3.3V
Package	SSOP 56
Speed	NA
Temperature	C
Status	Active
Sample	No
Minimum Order Quantity	104
Factory Order Increment	26

Distributor Inventory

No Pricing information is available from our Distributors at this time.

Documents

Type	Title	Size	Revision Date
Misc	PC Clocks Contact Info	61 KB	05/29/2007

Package

Description	SSOP 300 MIL, 56LD
Class	PLASTIC
Moisture Sensitivity Level (MSL)	1
Category	Green
Moisture Exposure Floor Life	Unlimited @ <30°C/85% RH
Peak Reflow Temperature	260°C
Rebake Conditions	N/A
Length	
Mark	G
Width	
Pitch	
Thickness	
Status	Active

Home | Site Map | Legal | Careers | Contact Us | Quality | RSS What is this?

Use of this website signifies your agreement to the acceptable use and privacy policy. Copyright 1997-2007 Integrated Device Technology, Inc. All Rights Reserved.