



T50L6M4

Standard Cable Tie, 15.35" Long, 50lb Tensile Strength, PA66, Blue, 1000/pkg

Article Number: 111-05434

Part Number: T50L6M4


Type: T50L



Base Data

Part No.	T50L6M4
Type	T50L
Color	Blue (BU)
Features	• Inside serrations allow for strong hold on cables and wire bundles. • Head design provides high tensile strength with very low insertion force. • Bent tail ensures a quick and simple installation.
Application Method	Quick, simple fixing by hand or with HellermannTyton tensioning tools
Identification Plate Position	none
Releasable Closure (Yes/No)	No
Tie Closure	plastic pawl
Typical Application	Used to bundle and secure wire and cable.
Variant	Inside Serrated

Product Dimensions



Min. Tensile Strength	50.0lbs / 225.0N
Length (L)	15.35" / 390.0mm

Width (W) (imperial)	0.18"
Width (W)	4.7mm
Min. Ø Bundle	0.06" / 1.5mm
Max. Ø Bundle	4.3" / 110.0mm

Material and Specifications

Material	Polyamide 6.6 (PA66)
US MILSPEC	MS3367-2-6
CSA Certified	No
Flammability	UL94 V2
Material Specification	HF / RoHS
Operating Temperature	-40 °F to +185 °F (-40 °C to +85 °C)
ROHS Conformity	 RoHS
Specification	UL ZODZ2.E64139
UL Listed (US and Canada)	Yes
UL Recognized (US and Canada)	Yes

Logistic and Packaging

Packaging Type	bag
Pkg. Qty.	1000
Carton Qty.	5000
EAN code	4031026416069
UPC	089306083924

© HellermannTyton North America 2011 | [TS16949](#), [ISO 9001](#) and [ISO 14001 Certified](#)
7930 N. Faulkner Rd. Milwaukee, WI 53224-9517 | Fax: 800-848-9866 | Phone: 800-537-1512