

Pressure screw set - HC-DS-PG11-E - 1675476

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)

Pg pressure screw set, standard version; for housing with Pg11 support; consisting of pressure screw, notched seal and 2 washers



Key commercial data

Packing unit	1 PCE
Minimum order quantity	10 PCE
Weight per Piece (excluding packing)	10.0 GRM
Custom tariff number	85369010
Country of origin	Germany

Technical data

Dimensions

Wrench size, union nut	18 mm
External cable diameter	7.5 mm ... 12.5 mm
Conductor sealing range	7.50 mm ... 12.50 mm

Ambient conditions

Degree of protection	IP65
Ambient temperature (operation)	-20 °C ... 80 °C

General

Material, pressure screw	Nickel-plated brass
Cable seal material	Perbunan
Thread type on connection side	Pg11

Pressure screw set - HC-DS-PG11-E - 1675476

Classifications

eCl@ss

eCl@ss 4.0	27141209
eCl@ss 4.1	27141209
eCl@ss 5.0	27149109
eCl@ss 5.1	27149109
eCl@ss 6.0	27149109
eCl@ss 7.0	27149109
eCl@ss 8.0	27149109

ETIM

ETIM 2.0	EC000441
ETIM 3.0	EC000441
ETIM 4.0	EC000441
ETIM 5.0	EC000441

UNSPSC

UNSPSC 6.01	30211808
UNSPSC 7.0901	39121408
UNSPSC 11	39121408
UNSPSC 12.01	39121408
UNSPSC 13.2	39121408

Approvals

Approvals

Approvals

GOST

Ex Approvals

Approvals submitted

Approval details

Pressure screw set - HC-DS-PG11-E - 1675476

Approvals



Drawings

Dimensioned drawing

