

MP-60102

H.264 & MJPEG Hardware Compression Card,
supports dual streams (H.264 & MJPEG),
with 4 Ports of Video & Audio Inputs.



Features

- Mini-PCI interface
- H.264 & MJPEG Hardware Compression
- 4-ch Video & Audio inputs
- Support D1
- Windows XP (32-bit), Linux (32-bit) SDK

Specifications		
Form Factor	Mini-PCI Type IIIB Interface	
Compression Format	H.264 & MJPEG Hardware Compression (Support Multi-stream : H.264 x 2+ MJPEG x 1)	
Video	Input	4 channels (BNC type)
	Output	1 x S-video & 1 x Composite (Coexistent, Call Monitor)
	Display Rate	4-ch : Total 120 fps (NTSC) / 100 fps (PAL) @ D1 resolution

	Recording Rate	4-ch : Total 120 fps (NTSC) / 100 fps (PAL) @ D1 resolution
Audio	Input	4 channels (RCA type)
	Output	1 x Phone jack
OS Support	Windows XP, Linux	
SDK	Windows SDK, Linux SDK	
Dimensions	60 x 45 (mm)	
Support	Support	

Accessories (For MP-60102 / MP-60102A)



Ordering Code	
MP-60102	4-ch H.264 Video & Audio Mini-PCI Capture Card with SDK
MP-60102A	4-ch H.264 Video & Audio Mini-PCI Capture Card with SCode DVR program

CMS Software	
Free remote software	Server software , simple client software , IE viewer
CMS Economic Version	64-channel software , see 4 DVRs simultaneously
CMS Profession Version	Full Economic functions, Group link function, eMAP