



Millenium Web Server XC10 Part number 88950124



- Up to 100 events managed (100 16-bit variables)
 - Modular plug-in housing for DIN rail mounting
 - Capable of driving all types of MODEM using AT commands
 - A local monitor can be connected on the Ethernet port for on-site configuration
 - 3 LEDs on the front panel indicate the presence of the power supply and network traffic or hard disk activity
- Functions :
- WEB monitoring
 - Archiving
 - Remote diagnostics, SMS and e.mail alarm management
 - Field bus management (MODBUS)

Part numbers

	Type	Supply
88950124	XC10	24 V DC

Specifications

General characteristics

Storage temperature (°C)	-40 °C → +70 °C
Maximum memory capacity	30 Mo on Compact Flash card
Protection rating	Front panel : IP40 Terminal block : IP20
Operating temperature	-5 → +55 °C
Certifications	CE
Protocol	Web service (Web server ; FTP server ; TELNET server ; SMTP client ; DNS/DynDNS client : DHCP client, UDP server) ; MODBUS RTU communication

Electrical characteristics

Tolerance	± 20 %
Absorbed power	7 VA
Maximum inrush current	4 A (10 ms)

Comments

Dimensions (mm)

XC10

