


BURNDY® Products FCI

Cable Ties

UNIRAP™

STANDARD CABLE TIES



18 Lb. Minimum Tensile Strength

STANDARD PACKAGE CATALOG NUMBER	MATERIAL	MAXIMUM BUNDLE DIAMETER In. [mm]	MINIMUM TENSILE STRENGTH Lbs. (N)	LENGTH In. [mm]	WIDTH In. [mm]	INSTALLATION TOOL	TOOL SETTING	BULK PACKAGE CATALOG NUMBER	
CT18075C	Natural Nylon 6/6	.75 [19]	18 (80)	4.00 [102]	.10 [2.5]	TWT1, MK7	Mini	CT18075M	
CT18075C0	Black Nylon 6/6 UV							CT18075M0	
CT18125C	Natural Nylon 6/6	1.25 [32]		5.67 [144]				CT18125M	
CT18125C0	Black Nylon 6/6 UV							CT18125M0	
CT18200C	Natural Nylon 6/6	2.00 [51]		8.00 [203]				CT18200M	
CT18200C0	Black Nylon 6/6 UV							CT18200M0	



30 Lb. Minimum Tensile Strength

STANDARD PACKAGE CATALOG NUMBER	MATERIAL	MAXIMUM BUNDLE DIAMETER In. [mm]	MINIMUM TENSILE STRENGTH Lbs. (N)	LENGTH In. [mm]	WIDTH In. [mm]	INSTALLATION TOOL	TOOL SETTING	BULK PACKAGE CATALOG NUMBER
CT30125C	Natural Nylon 6/6	1.25 [32]	30 (133)	6.00 [152]	.14 [3.6]	TWT1, MK7	Intermediate	CT30125M
CT30125C0	Black Nylon 6/6 UV							CT30125M0



40 Lb. Minimum Tensile Strength

STANDARD PACKAGE CATALOG NUMBER	MATERIAL	MAXIMUM BUNDLE DIAMETER In. [mm]	MINIMUM TENSILE STRENGTH Lbs. (N)	LENGTH In. [mm]	WIDTH In. [mm]	INSTALLATION TOOL	TOOL SETTING	BULK PACKAGE CATALOG NUMBER	
CT40200C	Natural Nylon 6/6	2.00 [51]	40 (178)	8.50 [216]	.15 [3.8]	TWT1, MK7	Intermediate	CT40200M	
CT40200C0	Black Nylon 6/6 UV							CT40200M0	
CT40300C	Natural Nylon 6/6	3.00 [76]		11.50 [292]				CT40300M	
CT40300C0	Black Nylon 6/6 UV							CT40300M0	
CT40400C	Natural Nylon 6/6	4.00 [102]		14.50 [368]				CT40400M	
CT40400C0	Black Nylon 6/6 UV							CT40400M0	



50 Lb. Minimum Tensile Strength

STANDARD PACKAGE CATALOG NUMBER	MATERIAL	MAXIMUM BUNDLE DIAMETER In. [mm]	MINIMUM TENSILE STRENGTH Lbs. (N)	LENGTH In. [mm]	WIDTH In. [mm]	INSTALLATION TOOL	TOOL SETTING	BULK PACKAGE CATALOG NUMBER	
CT50175C	Natural Nylon 6/6	1.75 [44]	50 (222)	8.00 [203]	.18 [4.6]	TWT1, MK7	Standard	CT50175M	
CT50175C0	Black Nylon 6/6 UV							CT50175M0	
CT50300C	Natural Nylon 6/6	3.00 [76]		11.75 [298]				CT50300M	
CT50300C0	Black Nylon 6/6 UV							CT50300M0	
CT50400C	Natural Nylon 6/6	4.00 [102]		15.50 [394]				CT50400M	
CT50400C0	Black Nylon 6/6 UV								CT50400M0

K-6