



HONEYWELL
PART NUMBER
89477

REV	DOCUMENT	CHANGED BY	CHECK
A	0003744	NM 13APR04	AK




PROPOSED MOUNTING HOLE




MOUNTING NUT (81942)
TORQUE NUT TO 50 IN. LBS. MAX


HONEYWELL PART NO., DATE CODE
(SEE NOTE 5) AND OPERATORS CLOCK
NUMBER TO BE PRINTED ON LABEL
AND AFFIXED TO THIS SURFACE



VIEW OF TERMINALS
SCALE 1:1



MATING CONNECTOR
DELPHI /PACKARD ELECTRIC
280 SERIES, 4 WAY METRIPACK
HOUSING: PN 12052856
TERMINALS : PN 12034046



FRONT VIEW

- NOTES
- 1 - OFF/IGN/IGN,HEAT/IGN, HEAT,START (RECOIL BACK TO IGN).
KEY REMOVABLE IN OFF POSITION.
 - 2 - NUT NOT INSTALLED, BUT IS SHIPPED ALONG WITH
SWITCHES PER PACK OP P/N 994400.
 - 3 - MAXIMUM ELECTRICAL RATING: 12 VOLT - 20 AMP
 - 4 - MATERIAL SPECIFICATION:
FRONT HOUSING - 40% MINERAL FILLED NYLON
BACK HOUSING - POLYPROPYLENE
NUT - 40% MINERAL FILLED NYLON
 - 5 - DATE CODE IS A 5 DIGIT NO., 1ST AND 2ND
DIGITS REPRESENT THE YEAR, THE NEXT
3 DIGITS REPRESENT THE DAY.
 - 6 - KEY CODE FOR SWITCH IS 6896.

SIM. TO: 88423

CUSTOMER PRINT

DESIGN UNITS: INCH			DRAWN	NM	13 APR 04	Honeywell			
TOLERANCES UNLESS NOTED:			CHECK	AK	13 APR 04				
NO PLACE	X	±	THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE PERMISSION OF HONEYWELL.	TITLE KEY SWITCH ASSY (4-POSITION)					
ONE PLACE	.X	±							
TWO PLACE	.XX	±							
THREE PLACE	.XXX	±							
FOUR PLACE	.XXXX	±							
ANGLES	X	±	INTERPRET PER ASME Y14.5M-1994 OTHER HONEYWELL ENGINEERING STANDARDS MAY APPLY	SIZE C	TYPE I	DRAWING NAME 89477		REV A	
THIRD ANGLE PROJECTION 			Pro/ENGINEER	3D	SCALE 2:1		SHEET 2 OF 2		