

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1212030005](#)
Status: **Active**
Overview: mPm DIN Valve Connectors
Description: mPm DIN Valve Connector, Form B-10mm, External Thread, 2 Pole Plus Ground Terminal, 250V AC/DC, Transparent, Nitrile Gasket



Documents:
[Drawing \(PDF\)](#) [Packaging Specification PK-121203-C92-001 \(PDF\)](#)
[Product Specification PS-121201-001-001 \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Product Specification STR-1251-001 \(PDF\)](#)

General
Product Family Field Attachable / Accessories
Series [121203](#)
Form B - 10mm
IP Rating IP65, IP67
Material - Contact Brass
Overview [mPm DIN Valve Connectors](#)
Product Name mPm
Type Field Attachable Connector
UPC 883906916299

Physical
Cable Diameter N/A
Coupling Type External Thread
Diagnostics / LEDs No
Diagnostics Port No
Gender N/A
Keyway None
Material - Connector Body Polyamide
Material - Coupling Nut N/A
Material - Plating Mating Silver
Net Weight 19.527/g
Orientation 90° Angle
Pitch - Mating Interface 10.00mm
Poles 2
Temperature Range - Operating -40°C to +90°C
Wire Size AWG N/A

Electrical
Current - Maximum per Contact 16.0A
Voltage - Maximum 250V AC/DC

Material Info
Engineering Number C92200T0T

Reference - Drawing Numbers
[Packaging Specification](#) PK-121203-C92-001
[Product Specification](#) PS-121201-001-001, STR-1251-001
[Sales Drawing](#) SD-121203-001

EU ELV
Not Relevant

EU RoHS **China RoHS**
Compliant with Exemption 6(c)
REACH SVHC
Contained Per - ED/71/2019 (16 July 2019)
Lead
Halogen-Free Status
Low-Halogen
For more information, please visit [Contact US](#)

China ROHS	50 Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series
[121203](#) Series