





HEAT SEALED



1. CABLE: NO UL, 28AWG(7/0.127), TINNED AND STRANDED COPPER WIRE
 INSULATOR: PVC, ID: 0.85mm, CABLING: 7C+DRAIN WIRE
 SHIELD: AL/MY COVERAGE
 JACKET: PVC, COMPLIANCE ROHS, COLOR: BEIGE, D.D: 5mm
2. 2PCS CONNECTOR: D-SUB 9 WAYS FEMALE SOLDER TYPE CONNECTOR
 INSULATOR: P.B.T.+GLASS FIBER, COLOR: BLUE
 CONTACT: COPPER ALLOY, GOLD FLASH OVER NICKEL PLATED
 SHELL: NICKEL PLATED.
 CONNECTOR COMPLIANCE ROHS
3. HOOD: PVC MOLDED TYPE WITH FOIL SHIELDED ON INNER
 ON INNER MOLD AND INJECTION OUTER MOLD WITH
 THUMB SCREW #4-40 UNC
 COLOR: BEIGE, COMPLIANCE ROHS
4. Fulfill ROHS Guideline
5. ELECTRONIC TEST
 100% OPEN SHORT+MISS WIRE TEST

DRAWING

DB9PIN JACK(J1)	WIRE	DB9PIN JACK(J2)
2		3
3		2
4		6
5		5
6		4
7		8
8		7
SHELL	DRAIN WIRE	SHELL

PART NO	4070-XX	SHEET NO	1	THIRD ANGLE PROJECTION
TITLE: DB9 PIN FEMALE TO DB9 PIN MALE BEIGE COLOR				SCALE N.T.S
				SIZE A4
				UNIT
DWN NO				APPROVED BY & DATE
				mm INCH