






LOC	DIST	REVISONS					
J	—	変更					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
			G4	OBSOLETE -5	ECR-08-000600	09JAN08	TS KB



- 注記:
- ①  面より2mmの範囲で測定のこと。
 - ② 相手ハウジングと所定の機能を満たしてかん合できること。
 - ③ フードの反りは0,2以内。
- 4 推奨取付けねじ: JIS B 1115 又は、1122 タッピンねじ
なべ1種又は2種、呼び径3長さ6mm以下
(締め付けトルク: 39,2N 以下)
- 5 適用製品規格 No.108-5093
- 6 相手ハウジングとのかん合力は、29,4N以下
ただし、リセプタクルコンタクトは含まない。
- ④ タブなしタイプ(表参照)回路番号下図参照のこと。

- NOTES;
- ⚠ TO BE MEASURED WITHIN 2mm FROM 
- ⚠ IN COUPLING WITH THE PLUG HOUSING MATING SATISFIES FUNCTION
- ⚠ WARPAGE 0.2 MAX.
- 4 RECOMMENDED MOUNTING SCREW; 3mmDIA, 6mmLENGTH(MAX.) PAN HEAD, CLASS 1 AND 2 TAPPING SCREW SPECIFIED IN JIS B1115, B1122 (TIGHTENING TORQUE; 39.2N MAX.)
- 5 SPEC. No. 108-5093
- 6 IN COUPLING WITH THE PLUG HOUSING MATING FORCE 29.4N MAX WITHOUT RECEPTACLE CONTACT
- ⚠ NON TAB CONTACT'S TYPE (SEE TABLE)
- CIRCUIT NUMBER 



	—//—	SELECTIVE-TIN (MATTE)	SELECTIVE GOLD (0.76μm MIN.)	NATURAL	5172040-8
	—//—	SELECTIVE-TIN (MATTE)	SELECTIVE GOLD (0.38μm MIN.)	NATURAL	1-5172040-5
	2	PRE-TIN		NATURAL	2-172040-1
OBSOLETE	—//—	TIN-LEAD	SELECTIVE GOLD (0.38μm MIN.)	GREEN	1-172040-8
	—//—	TIN-LEAD	SELECTIVE GOLD (0.38μm MIN.)	NATURAL	1-172040-5
OBSOLETE	—//—	TIN-LEAD	SELECTIVE GOLD (0.76μm MIN.)	YELLOW	1-172040-4
OBSOLETE	—//—	TIN-LEAD	SELECTIVE GOLD (0.76μm MIN.)	GRAY	1-172040-3
OBSOLETE	—//—	TIN-LEAD	SELECTIVE GOLD (0.76μm MIN.)	BLUE	1-172040-2
OBSOLETE	—//—	TIN-LEAD	SELECTIVE GOLD (0.76μm MIN.)	GREEN	1-172040-1
OBSOLETE	—//—	TIN-LEAD	SELECTIVE GOLD (0.76μm MIN.)	BROWN	1-172040-0
OBSOLETE	—//—	TIN-LEAD	SELECTIVE GOLD (0.76μm MIN.)	BLACK	172040-9
	—//—	TIN-LEAD	SELECTIVE GOLD (0.76μm MIN.)	NATURAL	172040-8
OBSOLETE	—//—	PRE-TIN		YELLOW	172040-7
OBSOLETE	—//—	PRE-TIN		BLUE	172040-5
	—//—	PRE-TIN		GREEN	172040-4
OBSOLETE	—//—	PRE-TIN		BROWN	172040-3
	—//—	PRE-TIN		BLACK	172040-2
	—//—	PRE-TIN		NATURAL	172040-1
	△NON TAB PLACES タブなし箇所	SOLDERING SIDE 半田付け部	CONTACT SIDE 接触部側	COLOR 色	PART NUMBER 製品型番
		CONTACT FINISH コンタクト仕上			

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN T.SHINOHARA 11AUG07		Tyco Electronics Tyco Electronics Corporation Kawasaki, Japan	
CHK K.BETSUI 11AUG07		APVD K.BETSUI 11AUG07		NAME 5P HORIZONTAL TYPE CAP HOUSING ASS'Y MULTI-INTERLOCK CONN. (WIRE TO P.C.B.)	
DIMENSIONS: 单位: 毫米 mm 		TOLERANCES UNLESS OTHERWISE SPECIFIED. 一般公差 0 PLC ± 1 PLC ± 2 PLC ± 3 PLC ± 4 PLC ± ANGLES ±		PRODUCT SPEC 製品規格 108-5093 APPLICATION SPEC 取付適用規格 —	
MATERIAL 材料 HSG: 66 NYLON CONTACT: BRASS		FINISH 仕上 —		WEIGHT —	
CUSTOMER DRAWING		SIZE A2		CAGE CODE 00779	
DRAWING NO 番号 C-172040		RESTRICTED TO —		SCALE 尺度 2:1	
SHEET 1 OF 1		REV G4			

TOLERANCE UNLESS
OTHERWISE SPECIFIED:
一般公差

$0 < x \leq 10$	: ± 0.2
$10 < x \leq 30$	: ± 0.25
$30 < x \leq 100$	: ± 0.3
ANGLE ; 角度	: $\pm 3^\circ$