

Series I Thermistors

2.2 to 100K Ohms Resistance @25°C
Thermally Conductive Epoxy Coating
Choice of 4 Temperature Tolerance
Classifications
Low Cost

SERIES I THERMISTORS


The BetaCURVE chip is soldered to 32 AWG Alloy 180 leads and encapsulated in Stycast epoxy resin

FEATURES


- 2.2 to 100K Ohms Resistance @25°C
- Proven Stability and Reliability
- Alloy lead wires for reduced thermal conductivity
- Interchangeability
- Thermally conductive epoxy coating
- Temperature range -40°C to +125°C
- RoHS Compliant

APPLICATIONS

- Tight tolerance instrumentation
- Temperature sensing, control and compensation
- Assembly into probes for a wide variety of applications
- General instrumentation applications



Dimensions



	Dimensions	
	A	B
	76 ± 2mm	2.4mm Max
Note 1	32 AWG Solid Alloy 180 Leads	
Note 2	Stycast 2850ft Epoxy	

Product Definition

Part Number	Color Coding	Resistance [Ω] @ +25°C	Tolerance from 0 to +70°C	Alpha Value @ +25°C	Beta Value 25/85	Beta Tolerance	Dissipation Constant in still air @ +25°C	Time response (Stirred Oil)
2.2K3A1A	Brown	2,252	±0.1°C	-4.39 %/ °C	3976	±0.5%	0.75 mW/°C	<1 second
2.2K3A1B			±0.2°C					
2.2K3A1C			±0.5°C					
2.2K3A1D			±1.0°C					
3K3A1A	Red	3,000	±0.1°C	-4.39 %/ °C	3976	±0.5%	0.75 mW/°C	<1 second
3K3A1B			±0.2°C					
3K3A1C			±0.5°C					
3K3A1D			±1.0°C					
5K3A1A	Orange	5,000	±0.1°C	-4.39 %/ °C	3976	±0.5%	0.75 mW/°C	<1 second
5K3A1B			±0.2°C					
5K3A1C			±0.5°C					
5K3A1D			±1.0°C					
10K3A1A	Yellow	10,000	±0.1°C	-4.39 %/ °C	3976	±0.5%	0.75 mW/°C	<1 second
10K3A1B			±0.2°C					
10K3A1C			±0.5°C					
10K3A1D			±1.0°C					
10K4A1A	Black	10,000	±0.1°C	-4.04 %/ °C	3694	±0.5%	0.75 mW/°C	<1 second
10K4A1B			±0.2°C					
10K4A1C			±0.5°C					
10K4A1D			±1.0°C					
30K5A1A	White	30,000	±0.1°C	-4.30 %/ °C	3942	±0.5%	0.75 mW/°C	<1 second
30K5A1B			±0.2°C					
30K5A1C			±0.5°C					
30K5A1D			±1.0°C					
30K6A1A	Green	30,000	±0.1°C	-4.68 %/ °C	4261	±0.5%	0.75 mW/°C	<1 second
30K6A1B			±0.2°C					
30K6A1C			±0.5°C					
30K6A1D			±1.0°C					
50K6A1A	Blue	50,000	±0.1°C	-4.68 %/ °C	4261	±0.5%	0.75 mW/°C	<1 second
50K6A1B			±0.2°C					
50K6A1C			±0.5°C					
50K6A1D			±1.0°C					
100K6A1A	Violet	100,000	±0.1°C	-4.68 %/ °C	4261	±0.5%	0.75 mW/°C	<1 second
100K6A1B			±0.2°C					
100K6A1C			±0.5°C					
100K6A1D			±1.0°C					

Reliability data

Test	Standard	Test conditions	$\Delta R_{25}/R_{25}$	Remarks
Storage in dry heat	IEC 60068-2-2	High temperature storage @+100°C. Duration: 1000 h	<0.5%	No mechanical damage
Storage in dry heat	IEC 60068-2-2	High temperature storage @+125°C. Duration: 1000 h	<1%	No mechanical damage
Storage in damp heat, steady state	IEC60068-2-78	Ambient Conditions: Temperature: +40°C. Relative humidity 93% Duration: 56 days	<1%	No mechanical damage
Rapid temperature cycling	IEC60068-2-14	Lower test temperature: -40°C Upper test temperature: +125°C Number of cycles: 1000	<1%	No mechanical damage
Endurance		Pmax: 60mW Duration: 1000 h	<2%	No mechanical damage

The information in this sheet has been carefully reviewed and is believed to be accurate; however, no responsibility is assumed for inaccuracies. Furthermore, this information does not convey to the purchaser of such devices any license under the patent rights to the manufacturer. Measurement Specialties, Inc. reserves the right to make changes without further notice to any product herein. Measurement Specialties, Inc. makes no warranty, representation or guarantee regarding the suitability of its product for any particular purpose, nor does Measurement Specialties, Inc. assume any liability arising out of the application or use of any product or circuit and specifically disclaims any and all liability, including without limitation consequential or incidental damages. Typical parameters can and do vary in different applications. All operating parameters must be validated for each customer application by customer's technical experts. Measurement Specialties, Inc. does not convey any license under its patent rights nor the rights of others.

Ordering Information

NORTH AMERICA

Measurement Specialties, Inc.
910 Turnpike Road
Shrewsbury, MA 01545
Tel: 1-508-842-0516
Fax: 1-508-842-0342

Sales email:
temperature.sales.amer@meas-spec.com

EUROPE

Measurement Specialties, Inc.
Ballybrit Business Park
Galway Ireland
Tel: +353-91-753238
Fax: +353-91-770789

Sales email:
temperature.sales.emea@meas-spec.com

ASIA

Measurement Specialties (China) Ltd.
No. 26 Langshan Road
Shenzhen High-Tech Park (North)
Nanshan District, Shenzhen 518057
China
Tel: +86 (0) 755 33305088
Fax: +86 (0) 755 33305099

Sales email:
temperature.sales.asia@meas-spec.com