

Kupfer-Aderendhülsen ohne Isolation

Embouts de fil en cuivre sans isolation


Uninsulated copper ferrules

DIN 46228/1

* ausgenommen
* excepté
* excepted

Werkstoff/Matière/Material
.4 = Kupfer/cuivre/copper

= Oberflächen/Surface/Surface-plating
Seite/page/page 5.011



mm ²	AWG	Artikelnummer Numéro d'article Part-No.	DIN	øD1 mm	øD2 mm	L1 mm	S mm	Werkzeuge Outils Toolings
0.1-0.3	26-24	440005.4	*	0.7	1.7	5	0.15	3984h, 4517, 4536, 4542
	26-24	440007.4	*	0.7	1.7	7	0.15	
	26-24	440010.4	*	0.7	1.7	10	0.15	
	26-24	440015.4	*	0.7	1.7	15	0.15	
0.34	24	449905.4	*	0.9	1.8	5	0.15	3984h, 4517, 4536, 4542
	24	449907.4	*	0.9	1.8	7	0.15	
0.5	22-20	440106.4	0.5-6	1	2.1	6	0.15	3983p.3, 3984j, 4521, 4523n, 4526n, 4531, 4536, 4542
	22-20	440108.4	*	1	2.1	8	0.15	
	22-20	440110.4	0.5-10	1	2.1	10	0.15	
	22-20	440112.4	*	1	2.1	12	0.15	
	22-20	440130.4	*	1	2.1	30	0.15	
0.75	20-18	440206.4	0.75-6	1.2	2.3	6	0.15	3983p.3, 3984j, 4521, 4522, 4526n
	20-18	440208.4	*	1.2	2.3	8	0.15	
	20-18	440210.4	0.75-10	1.2	2.3	10	0.15	
	20-18	440212.4	*	1.2	2.3	12	0.15	
	20-18	440220.4	*	1.2	2.3	20	0.15	
1	18	440306.4	1-6	1.4	2.5	6	0.15	3983p.3, 3984h, 4518n, 4523n, 4527, 4531, 4536, 4542
	18	440308.4	*	1.4	2.5	8	0.15	
	18	440310.4	1-10	1.4	2.5	10	0.15	
	18	440312.4	*	1.4	2.5	12	0.15	
	18	440320.4	*	1.4	2.5	20	0.15	
1.5	16	440406.4	*	1.7	2.8	6	0.15	3983p.3, 3984h, 4518n, 4523n, 4527, 4531, 4536, 4542
	16	440407.4	1.5-7	1.7	2.8	7	0.15	
	16	440408.4	*	1.7	2.8	8	0.15	
	16	440410.4	1.5-10	1.7	2.8	10	0.15	
	16	440412.4	1.5-12	1.7	2.8	12	0.15	
	16	440415.4	*	1.7	2.8	15	0.15	
	16	440418.4	1.5-18	1.7	2.8	18	0.15	
2.5	16	440420.4	*	1.7	2.8	20	0.15	3983p.3, 3984h, 4518n, 4523n, 4527, 4531, 4536, 4542
	14	440505.4	*	2.2	3.4	5	0.15	
	14	440506.4	*	2.2	3.4	6	0.15	
	14	440507.4	2.5-7	2.2	3.4	7	0.15	
	14	440508.4	*	2.2	3.4	8	0.15	
	14	440510.4	2.5-10	2.2	3.4	10	0.15	
	14	440512.4	2.5-12	2.2	3.4	12	0.15	
	14	440515.4	*	2.2	3.4	15	0.15	
	14	440518.4	2.5-18	2.2	3.4	18	0.15	
	14	440520.4	*	2.2	3.4	20	0.15	
4	14	440530.4	*	2.2	3.4	30	0.15	3983p.3, 3984h, 4518n, 4523n, 4527, 4531, 4536, 4542
	12	440608.4	*	2.8	4	8	0.2	
	12	440609.4	4-9	2.8	4	9	0.2	
	12	440610.4	*	2.8	4	10	0.2	
	12	440612.4	4-12	2.8	4	12	0.2	
	12	440615.4	4-15	2.8	4	15	0.2	
	12	440618.4	4-18	2.8	4	18	0.2	
	12	440620.4	*	2.8	4	20	0.2	
120	4/0	441532.4	*	16.5	19	32	0.5	4537, 4539n
	150	441632.4	*	18.5	21	32	0.5	

mm ²	AWG	Artikelnummer Numéro d'article Part-No.	DIN	øD1 mm	øD2 mm	L1 mm	S mm	Werkzeuge Outils Toolings
6	10	440704.4	*	3.5	4.7	4	0.2	3983p.3, 3984j, 4521, 4523n, 4526n, 4531, 4536, 4542
	10	440706.4	*	3.5	4.7	6	0.2	
	10	440710.4	6-10	3.5	4.7	10	0.2	
	10	440712.4	6-12	3.5	4.7	12	0.2	
	10	440715.4	6-15	3.5	4.7	15	0.2	
	10	440718.4	6-18	3.5	4.7	18	0.2	
	10	440720.4	*	3.5	4.7	20	0.2	
	10	440725.4	*	3.5	4.7	25	0.2	
	10	440730.4	*	3.5	4.7	30	0.2	
10	8	440812.4	10-12	4.5	5.8	12	0.2	3983p.3, 3984j, 4521, 4522, 4526n
	8	440815.4	10-15	4.5	5.8	15	0.2	
	8	440816.4	*	4.5	5.8	16	0.2	
	8	440818.4	10-18	4.5	5.8	18	0.2	
	8	440820.4	*	4.5	5.8	20	0.2	
16	8	440825.4	*	4.5	5.8	25	0.2	3984j, 4522, 4526n
	6	440912.4	16-12	5.8	7.5	12	0.2	
	6	440915.4	16-15	5.8	7.5	15	0.2	
	6	440918.4	16-18	5.8	7.5	18	0.2	
	6	440920.4	*	5.8	7.5	20	0.2	
	6	440922.4	*	5.8	7.5	22	0.2	
	6	440925.4	16-25	5.8	7.5	25	0.2	
25	6	440930.4	*	5.8	7.5	30	0.2	4522, 4538n, 4539n
	6	440932.4	16-32	5.8	7.5	32	0.2	
	4	441012.4	*	7.3	9.5	12	0.2	
	4	441015.4	25-15	7.3	9.5	15	0.2	
	4	441018.4	25-18	7.3	9.5	18	0.2	
	4	441020.4	*	7.3	9.5	20	0.2	
	4	441025.4	25-25	7.3	9.5	25	0.2	
35	4	441028.4	*	7.3	9.5	28	0.2	4522, 4538n
	4	441032.4	25-32	7.3	9.5	32	0.2	
	2	441112.4	*	8.3	11	12	0.2	
	2	441115.4	*	8.3	11	15	0.2	
	2	441118.4	35-18	8.3	11	18	0.2	
	2	441120.4	*	8.3	11	20	0.2	
	2	441125.4	35-25	8.3	11	25	0.2	
50	2	441130.4	*	8.3	11	30	0.2	4537, 4539n
	2	441132.4	35-32	8.3	11	32	0.2	
	1/0	441218.4	50-18	10.3	13	18	0.3	
	1/0	441220.4	*	10.3	13	20	0.3	
	1/0	441222.4	*	10.3	13	22	0.3	
	1/0	441225.4	50-25	10.3	13	25	0.3	
	1/0	441230.4	*	10.3	13	30	0.3	
70	1/0	441232.4	50-32	10.3	13	32	0.3	4537
	1/0	441240.4	*	10.3	13	40	0.3	
	2/0	441322.4	*	12.5	15	22	0.4	
	2/0	441325.4	*	12.5	15	25	0.4	
95	2/0	441332.4	*	12.5	15	32	0.4	4537
	3/0	441420.4	*	14.5	17	20	0.4	
	3/0	441425.4	*	14.5	17	25	0.4	
150	3/0	441432.4	*	14.5	17	32	0.4	4537
	3/0	441432.4	*	14.5	17	32	0.4	