

BRADY B-584 REFLECTIVE TAPE

TDS No. B-584

Effective Date: 08/12/2002

Description:

Brady B-584 is a reflective tape designed for use with the Labelizer® Plus Industrial Labeling System, GraphicsPro™ Label and Sign Creator, VersaPrinter™ Label and Sign Maker System, and the HandiMark® Portable Label Maker, PowerMark® Sign and Label Maker and GlobalMark™ Industrial Label Maker.

Details:



Use:

Brady B-584 is used in applications such as outdoor pole and pedestal identification and indoor long distance scanning of racks and shelves where high visibility is critical.

Adhesive Type:

Pressure sensitive acrylic: Class 1 (Fed. Spec. L-S-300)

Substrate Type:

Retroreflective sheeting: Type 1 (Fed. Spec. L-S-300)

Standard Material Colors:

Silver, yellow and orange

Standard Legend Colors:

Black, white, red, green, blue, yellow, magenta and cyan

Thickness (PSTC-33):

Total: 0.0055 in. (0.14mm)

Tensile Strength (PSTC-31):

Silver: 20 lb/in. (350 N/100mm)

Yellow and Orange: 10 lb/in. (175 N/100mm)

Elongation (PSTC-31):

Silver: 20%

Yellow and Orange: 118%

Adhesive Properties:

Adhesion to Steel (PSTC-1)

15 Minute Dwell (Avg.) -- 70 oz/in. (77 N/100mm)

Ultimate Dwell (72 Hrs.) (Avg.) -- Destroys

Tack (ASTM D 2979) (Avg.) -- 150 g (1.5 N)

Drop Shear (PSTC-7) (Avg.) -- >1200 Hrs.

Abrasion Resistance (Method 5306 of U.S. Federal Test Method Std. No. 191A):

CS-10 wheels, 250 g wts.

Legend withstands up to 100 cycles.

CS-10 wheels, 500 g wts.

Substrate withstands over 15,000 cycles.

Gloss:

100 Gardner Units

Reflectivity:

Reflectivity 1 (Fed. Spec. L-S-300)

Minimum Application Temperature:

Silver: 50°F (10°C)

Yellow and Orange: 0°F (-18°C)

Service Temperature:

-40°F to 158°F (-40°C to 70°C)

Average Outdoor Durability:

4-6 years (Average expected outdoor life of product will depend on user definition of failure, climatic conditions and mounting techniques.)

Chemical Resistance:

REAGENT	7 DAY IMMERSION	DIP TEST	RUB TEST
30% Sulfuric Acid	F	NE	NE
10% Sulfuric Acid	F	NE	NE
30% HCl	F	NE	NE
10% HCl	F	NE	NE
50% NaOH	F	NE	NE
10% NaOH	F	NE	NE
Methyl Ethyl Ketone	F	F	F
Acetone	F	F	F
1,1,1-Trichloroethane	F	F	F
Methanol	F	NE	F
IPA (Isopropanol)	F	NE	F
ASTM #3 Oil	NE	NE	NE
SAE 20 Oil	NE	NE	NE
Alconox®	NE	NE	NE
Toluene	F	F	F
Mineral Spirits	NE	NE	NE
Glacial Acetic Acid	F	F	F
5% Acetic Acid	F	NE	NE
Diesel Fuel	F	NE	NE
Heptane	F	NE	F
Conc. Ammonia	F	NE	NE
10% Ammonia	NE	NE	NE
Kerosene	F	NE	F
Water	NE	NE	NE
Gasoline	F	F	F
20% Sodium Carbonate	NE	NT	NE
2% Sodium Carbonate	NE	NT	NE
10% NaCl	NE	NT	NE
Bleach	NE	NT	NE

NE = No Effect

NT = Not Tested

F = Failed (affected Sample)

7 Day Immersion: Immersed in reagent for 7 days.

Dip Test: Five 10 minute dips in reagent with 30 minute recovery.

Rub Test: Rubbed sample for 1 minute with swab soaked in reagent.

Shelf Life:

1 year when stored at 70°F (21°C) and 40% to 50% R.H.

Trademarks:

Alconox® is a registered trademark of Alconox Co.
GraphicsPro™ is a trademark of Brady Worldwide, Inc.
HandiMark® is a registered trademark of Brady Worldwide, Inc.
Labelizer® is a registered trademark of Brady Worldwide, Inc.
Signmark® is a registered trademark of Brady Worldwide, Inc.
VersaPrinter™ is a trademark of Brady Worldwide, Inc.
GlobalMark™ is a trademark of Brady Worldwide, Inc.
PowerMark® is a registered trademark of Brady Worldwide, Inc.
ASTM: American Society for Testing and Materials (U.S.A.)
Fed. Spec.: United States Federal Specification (U.S.A.)
PSTC: Pressure Sensitive Tape Council (U.S.A.)
SAE: Society of Automotive Engineers (U.S.A.)
All S. I. Units (metric) are mathematically derived from the U.S. Conventional Units.

Note: All values shown are averages and should not be used for specification purposes.

Test data and test results contained in this document are for general information only and shall not be relied upon by Brady customers for designs and specifications, or be relied on as meeting specified performance criteria. Customers desiring to develop specifications or performance criteria for specific product applications should contact Brady for further information.

Product compliance information is based upon information provided by suppliers of the raw materials used by Brady to manufacture this product or based on results of testing using recognized analytical methods performed by a third party, independent laboratory. As such, Brady makes no independent representations or warranties, express or implied, and assumes no liability in connection with the use of this information.

WARRANTY

Brady products are sold with the understanding that the buyers will test them in actual use and determine for themselves their adaptability to their intended uses. Brady warrants to the buyers that its products are free from defects in material and workmanship, but limits its obligation under this warranty to replacement of the product shown to Brady's satisfaction to have been defective at the time Brady sold it. This warranty does not extend to any persons obtaining the product from the buyers. This warranty is in lieu of any other warranty, express or implied, including, but not limited to, any implied warranty of merchantability or fitness for a particular purpose, and of any other obligations or liability on Brady's part. Under no circumstances will Brady be liable for any loss, damage, expense, or consequential damages of any kind arising in connection with the use, or inability to use, Brady's products.

Copyright 2016 Brady Worldwide, Inc. | All Rights Reserved
Material may not be reproduced or distributed in any form without written permission.