





10 9 8 7 6 5 4 3 2 1




Wiring Diagram:

- 1 - WHITE / weiß
- 2 - BROWN / braun
- 3 - GREEN / grün
- 4 - YELLOW / gelb
- 5 - GREY / grau
- 6 - PINK / rosa
- 7 - BLUE / blau
- 8 - RED / rot



ITEM	COMPONENT	MATERIAL	FINISH
1	REC SHELL	BRASS	NICKEL PLATED
2	INSERT	PUR	BLACK
3	CONTACT	BRASS / GOLD	CuZn Ni/ Au
4	WIRES	COPPER/PVC	NONE
5	O-RING	NBR	BLACK
6	O-RING	VITON	RED
7	POTTING MATERIAL	EPOXY	NONE

POL	MATERIAL NO.	ENGINEERING NO.	FINISHED LENGTH
8	1200845095	WR8U20E02C300	300 ±10
8	1200845002	WR8U20E02M010	1000 ±10



VOLTAGE RATING: 30 VAC / 36 VDC
AMPERAGE RATING: 2 A
PROTECTION CLASS: IP 67/68/69K
OPERATING TEMPERATURE: -25°C / 90°C
UL CERTIFICATION: FILE NO. E152210
CSA CERTIFICATIONS: FILE NO. LR6837

ENTER DESCRIPTION EC NO: WEU2010-0298 DRWN:NSTAUDIGEL 2010/01/28 CHKD: 2010/02/01 APPR:FPACHER 2010/02/02	DESCRIPTION	QUALITY SYMBOLS ▽=0 ◻=0	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE 2:1	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION		
					DRAWN BY NSTAUDIGEL	DATE 2010/01/28	TITLE M12U 8-P FEMALE REC FRONT M16X1,5 0,25MM2				
					CHECKED BY	DATE					
					APPROVED BY FPACHER	DATE 2010/02/01	MOLEX INCORPORATED				
					MATERIAL NO.						
			DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SIZE A3		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION				
1		REV				SD-120084-019			1 OF 1		