

SNAP ACTION SWITCHES - SUB-MINIATURE




Contact Rating:	0.3A @ 6VDC
Electrical Life:	50,000 cycles typical
Mechanical Life:	100,000 cycles
Insulation Resistance:	100M ohms minimum @ 100VDC
Dielectric Strength:	250 VAC for 60 seconds
Operating Temperature:	-25C to 85C
Storage Temperature:	-30C to 85C

APPLICATIONS/MARKETS

- ▶ Sub miniature snap action switch
- ▶ Vertical and right angle pc pin termination
- ▶ Security/detection
- ▶ Appliance
- ▶ Instrumentation
- ▶ Power tools




HOW TO ORDER



Example Ordering Number

TS-01-01-F020-V1

Specifications subject to change without notice.






SERIES TS SWITCHES

SNAP ACTION SWITCHES - SUB-MINIATURE

TACT
SWITCHESNAVIGATION
SWITCHESPUSHBUTTON
SWITCHESTOGGLE
SWITCHESROCKER
SWITCHESSLIDE
SWITCHESSNAP-ACTION
SWITCHESDIP
SWITCHESKEYLOCK
SWITCHESROTARY
SWITCHESDETECTOR
SWITCHESCAP
OPTIONS

TERMINATION OPTIONS


P VERTICAL PC PINS




ACTUATOR BUTTON

Actuator	Operating Point
Type 1	6.7 ± 0.5


V1 PCB RIGHT ANGLE-SHORT



V2 PCB LEFT ANGLE-SHORT



V3 PCB RIGHT ANGLE-LONG



V4 PCB LEFT ANGLE-LONG

