









MATERIALS:

HOUSING - ZINC ALLOY, NICKEL PLATED
CONTACTS - COPPER ALLOY, SILVER PLATED
INSULATOR - THERMOPLASTIC, UL 94V-0 RATED
INSULATING SPACER - PHENOLIC
GROUND PIN - COPPER ALLOY, TIN PLATED
GROUND SPRING - HEAT TREATED STEEL OR COPPER ALLOY, TIN PLATED
RELEASE LEVER - C.R.S., NICKEL PLATED
LATCH SPRING - HEAT TREATED STEEL, NICKLE PLATED
FERRITE - NICKEL ZINC, K-100
RATED CURRENT - 3 AMP
SERVICE VOLTAGE - 133 VAC

RELEASE LEVER THROW 0.100 [2,5]



RECOMMENDED MOUNTING
PANEL LAYOUT



RECOMMENDED P.C. BOARD LAYOUT
(0.062 [1.57] THICK P.C. BOARD REF.)

						★ STAR SYMBOL DENOTES CRITICAL DIMENSION	UNLESS OTHERWISE SPECIFIED		THIS DRAWING DESCRIBES A DESIGN CONSIDERED PROPRIETARY IN NATURE, DEVELOPED AND MANUFACTURED BY SWITCHCRAFT INC. AND IS RELEASED ON A CONFIDENTIAL BASIS FOR IDENTIFICATION PURPOSES ONLY.									
									SIZE	WIDTH		MULT		LBS/M		TEMPER		
						1. ALL DIMENSIONS IN INCHES - TWO PLACE DECIMALS ±0.01 - THREE PLACE DECIMALS ±0.005 - ANGLES ±1° - ALL DIA. CONCENTRIC WITHIN 0.005 T.I.R.	FINISH		MATERIAL SPEC No.									
							SPEC No.											
						2. FEATURES ON THE SAME CENTERLINE MUST BE ALIGNED WITHIN ±0.002	FIRST USED ON		SCALE 3:1		Switchcraft®							
							DATE DRAWN		BY	CHKD					APVD			
B	24518	7/14/3	KJB	KJB		3. REMOVE ALL BURRS	21-Jan-02		KJB	TJK 1-21-02	KJB 1-21-02	SHEET OF						
A	22650	1-21-02	TJK	KJB			NAME		FEMALE 3 PIN OG RA/PC W/FERRITE									
REV	ECO NUMBER	DATE	BY	APVD		DO NOT SCALE DRAWING						PART No.		REV				
REVISIONS												F3FRAF		B				

CUSTOMER DRAWING

Switchcraft®