

PRODUCT NO.
10099439-002LF
10099439-003C-TRLF
10099439-004C-TRLF





A



B

C

D



SECTION G-G



spec ref				dr	Louis Ng	2010/05/01	projection 	MM 	size	A3	scale	2.000
tolerance std	TOLERANCES UNLESS OTHERWISE SPECIFIED			eng	Jeffrey Lim	2016/09/22			ecn no	ELX-S-24900-1		
ASME Y14.5				chr	-	-				rel level	Released	
				appr	Koon-Poh Tay	2016/10/06						
surface 	linear	0.X	±0.25	Amphenol FCi	title SAS PLUG R/A TYPE ASSY, Z-HT. 0.20				dwg no	10099439		rev G
		0.XX	±0.15									
		0.XXX	±0.050									
		angular	0°	±2°		cat. no.			Product - Customer Drw			sheet 1 of 3

PRODUCT NO.	WITH PICK-UP CAP	WITH ADHESIVE TAPE	PACKAGING
10099439-002LF	YES	NO	TRAY
10099439-002CLF			TAPE & REEL
10099439-003C-TRLF			
10099439-004C-TRLF		YES	






A



B

C




D



10099439-002 WITH PICK-UP CAP ATTACHED





3



10099439-003 WITH PICK-UP CAP ATTACHED

spec ref				dr	Louis Ng	2010/05/01	projection	MM	size	A3	scale	2.000	
tolerance std ASME Y14.5	TOLERANCES UNLESS OTHERWISE SPECIFIED			eng	Jeffrey Lim	2016/09/22			ecn no	ELX-S-24900-1			
				chr	-	-							
				appr	Koon-Poh Tay	2016/10/06							product family
surface 	linear	0.X	±0.25	Amphenol FCi	title	SAS PLUG R/A			dwg no	10099439		rev	G
		0.XX	±0.15										
		0.XXX	±0.050										
	angular	0°	±2°		cat. no.	Product - Customer Drw				sheet 2 of 3			

PRODUCT NO.
SEE TABLE



- NOTES:
- MATERIAL:
HOUSING & CAP: HIGH TEMPERATURE THERMOPLASTIC, BLACK, UL94V-0
 ADHESIVE TAPE: POLYIMIDE
CONTACT & HOLD DOWN: COPPER ALLOY
 - FINISH:
CONTACT: 1.27um MIN. Ni UNDERPLATE OVERALL,
1.91um MIN. 100% MATTE Sn(LEAD-FREE) ON SOLDER TAIL,
0.76um MIN. Au ON CONTACT AREA
HOLD DOWN: 1.91um MIN. 100% MATTE Sn(LEAD-FREE) OVER
1.27um MIN. Ni UNDERPLATE OVERALL
 - RECOMMENDED PCB THICKNESS: 1.00mm
 - PRODUCT SPECIFICATION: GS-12-282
 - PACKAGING SPECIFICATION: GS-14-952(TRAY); GS-14-1038(TAPE & REEL)
 - THIS PRODUCT MEETS EUROPEAN UNION DIRECTIVES AND OTHER
COUNTRY REGULATIONS AS DESCRIBED IN GS-47-0004
 - THE HOUSING WILL WITHSTAND EXPOSURE TO 260°C PEAK TEMPERATURE
FOR 10 SECONDS IN A CONVECTION, INFRA-RED OR VAPOR PHASE
REFLOW OVEN
 - A SYMBOL WILL BE NEXT TO ANY DIMENSION, VIEW OR NOTE WHICH
HAS BEEN MODIFIED WITH THE CURRENT DRAWING REVISION

spec ref				dr	Louis Ng	2010/05/01	projection		MM		size	A3	scale	1.000
tolerance std	TOLERANCES UNLESS OTHERWISE SPECIFIED			eng	Jeffrey Lim	2016/09/22					ecn no	ELX-S-24900-1		
				chr	-	-								
ASME Y14.5				appr	Koon-Poh Tay		2016/10/06	product family			rel level	Released		
surface	linear	0.X	±0.25	Amphenol FCI	title	SAS PLUG R/A TYPE ASSY, Z-HT. 0.20			dwg no	10099439			rev	G
		0.XX	±0.15											
		0.XXX	±0.050											
	angular	0°	±2°	cat. no.	Product - Customer Drw			sheet 3 of 3						