


COMBICON Plugs,
Pitch 5.0 or 5.08 mm



MSTB plugs with plug-in direction parallel to the conductor axis are available with a 5.0 mm or 5.08 mm pitch and 2 to 24 positions.

MSTB plugs with strain relief are available with a 5.0 mm pitch and 8 to 16 positions and with a 5.08 mm inch pitch and 3 to 16 positions.

MSTBP plugs with test connection for 2 or 2.3 mm Ø test plugs are available with 2 to 24 positions, and a 5.0 mm metric or a 5.08 mm inch pitch.


The plugs are available with and without a screw flange (STF), to permit a vibration-resistant connection with the headers.

The self-adhesive marker cards SK 5/3,8 or SK 5,08/3,8 are used for labeling (order data, see page 210).

The combination possibilities for plug connectors are documented in the COMBICON cross-reference list on pages 82 to 85.

Articles printed in bold can be delivered at short notice.

Products with black or gray housing available on request.



MSTB 2,5/...-ST

Plug-in direction parallel to the conductor axis

Pitch 5.0 or 5.08

(IEC)	rigid	flexible	I	U
[mm ²]	solid	stranded	AWG	[A] [V]
Connection data	0.2-2.5	0.2-2.5	24-12	12 250
Further technical data see page 220.				

Note:

Only actuate COMBICON plug connectors when under no load condition. If for operating reasons small loads must be switched, experimental values are available upon request.

Description	No. of positions	Dim. a [mm]	Type	Order No.	Pcs. Pkt.
Plugs, 5.0 mm pitch, color: green	2	5	MSTB 2,5/2-ST	17 54 44 9	50
	3	10	MSTB 2,5/3-ST	17 54 46 5	
	4	15	MSTB 2,5/4-ST	17 54 48 1	
	5	20	MSTB 2,5/5-ST	17 54 50 4	
	6	25	MSTB 2,5/6-ST	17 54 52 0	
	7	30	MSTB 2,5/7-ST	17 54 54 6	
	8	35	MSTB 2,5/8-ST	17 54 56 2	
	9	40	MSTB 2,5/9-ST	17 54 58 8	
	10	45	MSTB 2,5/10-ST	17 54 60 1	
	11	50	MSTB 2,5/11-ST	17 54 62 7	
	12	55	MSTB 2,5/12-ST	17 54 64 3	
	13	60	MSTB 2,5/13-ST	17 54 66 9	
	14	65	MSTB 2,5/14-ST	17 54 68 5	
	15	70	MSTB 2,5/15-ST	17 54 70 8	
	16	75	MSTB 2,5/16-ST	17 54 72 4	
	17	80	MSTB 2,5/17-ST	17 54 74 0	
	18	85	MSTB 2,5/18-ST	17 54 76 6	
	19	90	MSTB 2,5/19-ST	17 54 78 2	
	20	95	MSTB 2,5/20-ST	17 54 80 5	
	21	100	MSTB 2,5/21-ST	17 54 82 1	
	22	105	MSTB 2,5/22-ST	17 54 84 7	
	23	110	MSTB 2,5/23-ST	17 54 86 3	
	24	115	MSTB 2,5/24-ST	17 54 88 9	
Plugs, 5.08 mm pitch, color: green	2	5.08	MSTB 2,5/2-ST-5,08	17 57 01 9	50
	3	10.16	MSTB 2,5/3-ST-5,08	17 57 02 2	
	4	15.24	MSTB 2,5/4-ST-5,08	17 57 03 5	
	5	20.36	MSTB 2,5/5-ST-5,08	17 57 04 8	
	6	25.40	MSTB 2,5/6-ST-5,08	17 57 05 1	
	7	30.48	MSTB 2,5/7-ST-5,08	17 57 06 4	
	8	35.56	MSTB 2,5/8-ST-5,08	17 57 07 7	
	9	40.64	MSTB 2,5/9-ST-5,08	17 57 08 0	
	10	45.72	MSTB 2,5/10-ST-5,08	17 57 09 3	
	11	50.80	MSTB 2,5/11-ST-5,08	17 57 10 3	
	12	55.88	MSTB 2,5/12-ST-5,08	17 57 11 6	
	13	60.96	MSTB 2,5/13-ST-5,08	17 57 12 9	
	14	66.04	MSTB 2,5/14-ST-5,08	17 57 13 2	
	15	71.12	MSTB 2,5/15-ST-5,08	17 57 14 5	
	16	76.20	MSTB 2,5/16-ST-5,08	17 57 15 8	
	17	81.28	MSTB 2,5/17-ST-5,08	17 57 16 1	
	18	86.36	MSTB 2,5/18-ST-5,08	17 57 17 4	
	19	91.44	MSTB 2,5/19-ST-5,08	17 57 18 7	
	20	96.52	MSTB 2,5/20-ST-5,08	17 57 19 0	
	21	101.60	MSTB 2,5/21-ST-5,08	17 57 20 0	
	22	106.68	MSTB 2,5/22-ST-5,08	17 57 21 3	
	23	111.76	MSTB 2,5/23-ST-5,08	17 57 22 6	
	24	116.84	MSTB 2,5/24-ST-5,08	17 57 23 9	

- (1) Test plug, consisting of metal part and colored insulating sleeve;
(2) Reducing plug, see page 207



Screwdriver SZS 0,6 x 3,5 see page 120.

