



REV.	DATE	DESCRIPTION
NC	03/12/97	INITIAL RELEASE
A	04/22/07	UPDATE DRAWING FORMAT



					UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN [] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY.	APPROVALS		DATE		Amphenol Connex						
B						DRAWN	G.R.S.	04/22/07								
7					UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE: 0.5 - 8mm ± 0.20mm 8 - 30mm ± 0.40mm 30 - 120mm ± 0.50mm	CHECKED				PART DESCRIPTION TNC PANEL DIRECT SOLDER JACK .085" SEMI-RIGID CABLE						
6						ISSUED										
5	SOLDER NUT	BRASS	GOLD	1	UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE: .020 - .315 = ± 0.007" .315 - 1.180 = ± 0.015" 1.180 - 4.724 = ± 0.020"	SHEET		1 OF 1		PART NO. 122389						
4	INSULATOR	TEFLON	NATURAL	1		CAD FILE		C:/122/122389.DWG								
3	CONTACT PIN	PHOS. BRONZE	GOLD	1	DO NOT SCALE DRAWING					DWG. NO.		122389.DWG	REV. A	SIZE A	SCALE NA	
2	INSULATOR	TEFLON	NATURAL	1												
1	BODY	BRASS	NICKEL	1												
	DESCRIPTION	MATERIAL	FINISH	QTY												

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[122389](#)