



4

3




2

1


LOC	DIST	REVISIONS					
DW	—	P	LTR	DESCRIPTION		DATE	APVD
			A1	REVISED PER ECO-11-005301		6APR11	HMR



RECOMMENDED PCB LAYOUT



2 PIN



3 PIN

0.36g	17.50	19.30	20.50	15	1-1734829-5
0.34g	16.25	18.05	19.25	14	1-1734829-4
0.32g	15.00	16.80	18.00	13	1-1734829-3
0.30g	13.75	15.55	16.75	12	1-1734829-2
0.27g	12.50	14.30	15.50	11	1-1734829-1
0.26g	11.25	13.05	14.25	10	1-1734829-0
0.23g	10.00	11.80	13.00	09	1734829-9
0.21g	8.75	10.55	11.75	08	1734829-8
0.19g	7.50	9.30	10.50	07	1734829-7
0.16g	6.25	8.05	9.25	06	1734829-6
0.14g	5.00	6.80	8.00	05	1734829-5
0.12g	3.75	5.55	6.75	04	1734829-4
0.10g	2.50	4.30	5.50	03	1734829-3
0.08g	1.25	3.05	4.25	02	1734829-2
WEIGHT	C	B	A	NO. OF CONTACTS	PART NUMBER
	DIMENSIONS				

- NOTE:
- MATERIAL:
HOUSING: PA9T WITH 33% GF, UL 94V-0, NATURE COLOR.
CONTACTS: PHOSPHOR BRONZE.
 - FINISH:
CONTACTS: 2.54μm [100μ"] MIN. MATTE-TIN OVER
1.27μm [50μ"] MIN. NICKEL ON ENTIRE CONTACT.
 - WAVE SOLDER CAPABLE TO 265°C PER **TE Connectivity** TEST SPEC. 109-202, CONDITION B.

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:MM

MATERIAL

SEE NOTE

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ± 0.5

1 PLC ± 0.38

2 PLC ± 0.25

3 PLC ± 0.15

4 PLC ± -

ANGLES ± -

FINISH

SEE NOTE

DWN H. HUANG 31MAY2007

CHK S. HOU 31MAY2007

APVD W.J. KE 31MAY2007

PRODUCT SPEC 108-57499

QUALIFICATION TEST REPORT 501-57573

WEIGHT SEE TABLE

CUSTOMER DRAWING

TE Connectivity

NAME 1.25MM PITCH, WIRE TO BOARD CONNECTOR HEADER, R/A, DIP TYPE

SIZE A3

CAGE CODE 00779

DRAWING NO C-1734829

RESTRICTED TO

SCALE

SHEET 1 OF 2

REV A1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

—, —

© COPYRIGHT — BY — ALL RIGHTS RESERVED.

LOC

DIST

REVISIONS

DW

—

P

LTR


DESCRIPTION

DATE


DWN

APVD

SEE SHEET 1.



5.95 Kg	2.18 Kg	30	200	6000 PCS	15
5.92 Kg	2.15 Kg	32		6400 PCS	14
5.92 Kg	2.15 Kg	34		6800 PCS	13
5.96 Kg	2.19 Kg	36		7200 PCS	12
5.87 Kg	2.10 Kg	39		7800 PCS	11
5.97 Kg	2.20 Kg	43		8600 PCS	10
5.97 Kg	2.20 Kg	47		9400 PCS	09
5.95 Kg	2.18 Kg	52		10400 PCS	08
5.97 Kg	2.21 Kg	58		11600 PCS	07
5.85 Kg	2.11 Kg	66		13200 PCS	06
5.93 Kg	2.16 Kg	76		15200 PCS	05
5.93 Kg	2.16 Kg	90		18000 PCS	04
5.95 Kg	2.18 Kg	110		22000 PCS	03
5.92 Kg	2.14 Kg	141		28200 PCS	02
GROSS WEIGHT	NET WEIGHT	PCS/TUBE	TUBES /CARTON	QUANTITY	NO. OF POS.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN H. HUANG 31MAY2007	 TE Connectivity			
		CHK S. HOU 31MAY2007				
		APVD W.J. KE 31MAY2007				
		PRODUCT SPEC				
DIMENSIONS: MM		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME		
		0 PLC ± —		1.25MM PITCH, WIRE TO BOARD CONNECTOR HEADER, R/A, DIP TYPE		
		1 PLC ± —				
		2 PLC ± —				
		3 PLC ± —				
4 PLC ± —		APPLICATION SPEC				
MATERIAL		FINISH		SIZE		
				CAGE CODE		
				DRAWING NO		
				RESTRICTED TO		
				A300779		
				C=1734829		
				REV		
				A1		
				SCALE		
				SHEET		
				2 OF 2		
				CUSTOMER DRAWING		