




1064338-1
PART
NUMBER

<u>CONNECTOR</u>		
OUTER CONTACT	BERYLLIUM COPPER	GOLD PLATE
CENTER CONTACT	BERYLLIUM COPPER	GOLD PLATE
DIELECTRIC	POLYPROPYLENE, GF	N/A
<u>CABLE</u>		
JACKET	POLYVINYL CHLORIDE (PVC)	N/A
SHIELD	SILVER PLATED COPPER WIRE, 38 AWG	N/A
DIELECTRIC	PERFLUOROALKOXY (PFA)	N/A
CENTER CONDUCTOR	SILVER PLATED COPPER CLAD STEEL, 30 AWG	N/A
INSULATING DISK	POLYESTER	N/A
COMPONENT	MATERIAL	FINISH

<u>ELECTRICAL</u>			
FREQUENCY		DC — 6 GHz	
NOMINAL IMPEDENCE		50 OHMS	
VOLTAGE RATING		250 VOLTS (VRMS MAX) @ SEA LEVEL	
VSWR (MATED CONNECTORS ONLY)		1.20:1 MAX @ 2 GHz 1.40:1 MAX @ 6 GHz	
INSULATION RESISTANCE		1,000 MEGOHMS MIN	
DIELECTRIC WITHSTANDING VOLTAGE		500 VOLTS (VRMS MIN) @ SEA LEVEL	
<u>MECHANICAL</u>			
CONNECTOR DURABILITY		100 MATING CYCLES	
<u>ENVIRONMENTAL</u>			
TEMPERATURE RATING		-40°C(-40°F) TO +105°C(221°F)	
PRODUCT SPEC			
THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 24MAY91	
		P.RESNIC	
		CHK	
DIMENSIONS: mm		APVD <i>PRESNIC</i> 05/13/92	
TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME	
0 PLC ± -		OSMT RIGHT ANGLE JACK	
1 PLC ± -		PIGTAIL ASSY	
2 PLC ± -			
3 PLC ± -			
4 PLC ± -			
ANGLES ± -			
MATERIAL		SIZE CAGE CODE DRAWING NO	
FINISH		RESTRICTED TO	
-		A2 00779 C=1064338	
CUSTOMER DRAWING		SCALE 12:1 SHEET 1 OF 1 REV B	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[9950-2305-23](#)