





-
- PIN A1
- KEEP-OUT ZONE
- 28.50
- 0.95
- 1.90 TYP
- 2.95
- 20.8
- 14.85
- 11.42
- 1.35 TYP
- SIGNAL HOLES REF
- GROUND HOLE REF
- ROW A
- ROW B
- ROW C
- ROW D
- ROW E
- ROW F
- ROW G
- ROW H
- ROW J
- ROW K
- ROW L
- ROW M
- Ø 3.56±0.08
- Ø 0.15 UNPLATED SCREW HOLE
- 4.75
- 192X Ø0.46±0.05 PLATED THRU HOLE
- 192X Ø0.55±0.013 DRILL HOLE
- Ø 0.10
- LEFT GUIDED BACKPLANE HOLE PATTERN (CONNECTOR SIDE)




THIS DRAWING IS A CONTROLLED DOCUMENT.		OWN KIRAN HOLA		11JAN2013		 TE Connectivity	
DIMENSIONS:		CHK D. DIXON		11JAN2013			
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APP'D D. DIXON		11JAN2013		NAME	
mm		PRODUCT SPEC		[IMPACT, 4 PAIR, 16 COLUMN, HEADER LEFT GUIDED, OPEN END WALL SIGNAL MODULE, 0.46 PTH			
		APPLICATION SPEC		SIZE		CAGE CODE	
0 PLC ± 2 PLC ±0.25 2 PLC ±0.13 2 PLC ± 2 PLC ± ANGLES ± FINISH		WEIGHT		DRAWING NO		RESTRICTED TO	
		SEE TABLE		A100779		C=2007824	
		CUSTOMER DRAWING		SCALE		SHEET	
				6:1		1 of 2	
						REV A	

LOC	DIST	REVISIONS					
AD	00	P	LTR	DESCRIPTION	DATE	DWN	APVD
		-		SEE SHEET 1	-	-	-


	H	5.5	8-2007824-3	OBSOLETE
	H	4.9	8-2007824-2	
	H	4.5	8-2007824-1	
	G	5.5	7-2007824-3	
	G	4.9	7-2007824-2	
	G	4.5	7-2007824-1	
	F	5.5	6-2007824-3	
	F	4.9	6-2007824-2	
	F	4.5	6-2007824-1	
	E	5.5	5-2007824-3	
	E	4.9	5-2007824-2	
	E	4.5	5-2007824-1	
	D	5.5	4-2007824-3	
	D	4.9	4-2007824-2	
	D	4.5	4-2007824-1	
	C	5.5	3-2007824-3	
	C	4.9	3-2007824-2	
	C	4.5	3-2007824-1	
	B	5.5	2-2007824-3	
	B	4.9	2-2007824-2	
	B	4.5	2-2007824-1	
	A	5.5	1-2007824-3	
	A	4.9	1-2007824-2	
	A	4.5	1-2007824-1	
	-	5.5	2007824-3	
	-	4.9	2007824-2	
	-	4.5	2007824-1	
FINISH	KEY POSITION	DIM M	PART NUMBER	

REFER TO WWW.TE.COM
FOR PRODUCT AVAILABILITY


KEY POSITION
CHART



NONE




A




E




B




F




C



G



D



H