



Product Number: 713-1104

FEMALE CONNECTOR 4X2 POLE PIN SPACING 3.5 MM / 0.138 IN 100% PROTECTED AGAINST MISMATING

RoHS compliant

Packing unit 50 pieces

Weight	4.33 g
Color	black
No. of connection Points	8
No. of potentials	8
pole count	8
Height	18.8 mm
Height	0.74 in
Width	15.5 mm
Width	0.61 in
Depth	16 mm
Depth	0.63 in
Pin spacing from	3.5 mm
Pin spacing from	0.138 in
Pollution degree	2
Measured voltage EN	160 V
Measured shock voltage	2.5 kV
Current intensity EN	10 A
Pollution degree	2
Measured voltage EN	250 V
Measured shock voltage	2.5 kV
Current intensity EN	10 A
Connection method	CAGE CLAMP® CONNECTION
Cross section [mm²]	0.08 - 1.5 mm²
Wiring method	solid
Cross section [mm²]	0.08 - 1.5 mm²
Cross section [mm²]	0.25 - 1 mm²
Cross section [mm²]	0.25 - 1 mm²
Cross section [AWG]	28 - 16 AWG
Strip length from	6 mm
Strip length to	7 mm
Material group	II
Customs Tariff No.	85366990
Country of Origin	Deutschland