



NOTES:

1. ALL DIMENSION IN MM [INCH]
 2. GENERAL TOLERANCE: $X.X = \pm 0.4$
 $X.XX = \pm 0.25$
 3. TERM. NOS. FOR REF. ONLY
 4. CONTACT RATING SWITCHING: 150mA, 250V AC/DC
350mA, 110V AC/DC
 5. OPERATING FORCE: 425±100 CM/STANDARD
 6. OPERATING TEMP: -30° to 85°C
 7. CIRCUIT 4POLE: 3 POSITIONS, 30° INDEX.
 8. DIELECTRIC STRENGTH: 1000V RMS min.@SEA LEVEL.
 9. ▲ DESIGNATE MAJOR DIMENSIONS
 10. HARDWARE SUPPLIED ON SWITCH -SEE BELOW
- LOCKING RING, LOCKWASHER, & HEX NUT.





CONTACT CONFIGURATION

Timing: SHORTING



TERMINATION DETAIL

SCALE 2X



E-SWITCH®				
TITLE KC43A30.001SLS				
REV B				
DATE 3/25/03				
DR AR				
DWG G510269				
SCALE 1.5:1				