




Dimensions: mm (In.)

Type	Wire	Rating	Wire Color
441-R347A	12AWG	30A 32 VDC	Red
441-R347B	14AWG	20A 32 VDC	Red
441-R347C	16AWG	15A 32 VDC	Red
441-R347D	18AWG	10A 32 VDC	Red

SPECIFICATIONS	
Rating:	12-24 VDC
Contact Resistance:	50m Ω max.
Insulation Resistance:	500VDC 100M Ω min.
Dielectric Strength:	1500 VAC, 1 minute
Terminals:	Copper Alloy Tin (Sn) Plated
Body:	PVC

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Eagle Plastic Devices:

[441-R347A](#) [441-R347D](#) [441-R347C](#) [441-R347B](#)