


MALLORY**Mallory Sonalert Products Inc.****Part # SC250HP****Sales Outline Drawing****Revision****C****Specifications:**

| | |
|-------------------------|-------------------------------------|
| Sound level Category | Medium Sound Level |
| Mode of Operation | High Frequency, Fast Pulse |
| Mounting | Panel (see note B) |
| Voltage Rating | 60 to 250 Vac/dc |
| Frequency | 4500 Hz \pm 500 Hz |
| Loudness (Min. Voltage) | 68 dB (A) min. @ 2 FT and 60 Vac/dc |
| Loudness (Max Voltage) | 80 dB(A) min. @ 2FT and 250 Vac/dc |
| Current Draw | 5 mA Max @ 60 Vac/dc |
| Current Draw | 16 mA Max @ 250 Vac/dc |
| Min. Pulse Rate (PPS) | 2 @ 60 Vac/dc |
| Max. Pulse Rate (PPS) | 10 @ 250 Vac/dc |
| Duty Cycle (%) | 50 (Approx) |
| Storage Temperature | -40°C to +85°C |
| Operating Temperature | -30°C to +65°C |
| Weight (Typical) | 2.1 oz (60 g) |
| Housing | 6/6 Nylon, Color Black |
| Options | For other options contact factory |

Dimensions: Inches (mm)

PART DIMENSIONS BEFORE CODE DATE 0824 5 PART DIMENSIONS AFTER CODE DATE 0825 1



NOTE A: TERMINALS-.032 BRASS TIN PLATED, TAPPED FOR #6-32 SCREW. TWO #6-32 NICKEL PLATED BRASS SCREWS INCLUDED. WILL ACCEPT 1/4" QUICK CONNECT.

NOTE B: MOUNTING- REMOVE BLACK PLASTIC NUT AND INSERT THREADED FRONT THROUGH 125° HOLE PUNCHED IN PANEL, IF ORIENTATION IS NEEDED, NOTE LOCKING FLATS ON DRAWING. SCREW NUT BACK ON. DO NOT OVERTIGHTEN.

NOTE A: TERMINALS-.032 BRASS TIN PLATED, TAPPED FOR #6-32 SCREW. TWO #6-32 NICKEL PLATED BRASS SCREWS INCLUDED. WILL ACCEPT 1/4" QUICK CONNECT.

NOTE B: MOUNTING- REMOVE BLACK PLASTIC NUT AND INSERT THREADED FRONT THROUGH 125° HOLE PUNCHED IN PANEL, IF ORIENTATION IS NEEDED, NOTE LOCKING FLATS ON DRAWING. SCREW NUT BACK ON. DO NOT OVERTIGHTEN.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Mallory Sonalert:](#)

[SC250HP](#)