




Integrated Device Technology

The Analog and Digital Company™

[Products](#) | [Applications](#) | [Search](#) | [Support](#) | [Investor](#) | [About IDT](#)[9LRS4123A](#)  [9LRS4123AKLF](#)

9LRS4123AKLF

[Description](#) | [Parameters](#) | [Package](#) | [Documents](#) | [Distributor Inventory](#) | [Contacts](#)

DESCRIPTION

PC MAIN CLOCK - PIKETON

Generic Part:

[9LRS4123A](#)

Category:

PARAMETERS

Package VFQFPN 32
Voltage 1.8V/3V
Temperature C
Speed NA

PACKAGE

Package [VFQFPN 32 \(NLG32\)](#)
Description VFQFP-N 5 X 5 X 1.0MM NO LEAD
Status Active
Class PLASTIC
Category [Green](#)
Pb (Lead) Free [Yes](#)
Pb Free Category [e3 Sn](#)
Mark K
Package Type VFQFPN
Lead Count 32
Length 5.0 mm
Width 5.0 mm
Thickness 1.0 mm
Pitch 0.5 mm
Tube / Tray TRAY
Quantity per Tube/Tray 490
Quantity per Reel 2500
Moisture Sensitivity Level (MSL) 3
Moisture Exposure hrs@<30C/60% RH
Peak Reflow Temperature 260°C
Rebake Conditions 48hrs@125C
Related Package Documents [view documents](#)

DOCUMENTS

Type	Title	Size	Revision Date
Product Change Notice	PCN# : A1004-01(R1) Alternate Assembly Facilities for VFQFPN-32	131 KB	06/04/2010
	PCN# : A1004-01 Alternate Assembly Facilities for VFQFPN-32	130 KB	04/02/2010
	PCN# : A0910-01 Alternate Assembly Facility for Copper Wire Process on VFQFPN-20, 32, 40, 48, 56	117 KB	11/05/2009

DISTRIBUTOR INVENTORY

Part	Distributor	Qty	Date	RFQ	Order
No matches found.					

CONTACTS

Sales Offices

► [Sales Offices and authorized distributors](#)

Technical Support

Clock Help

► WWW: [Clock Help](#)

Copyright © 2011 Integrated Device Technology, Inc. | [Legal](#) | [Careers](#) | [Contact Us](#) | [myIDT](#) | [Press Room](#) | [Site Map](#)