




Terminal blocks

to Type 329

	ASP045	page 49
	Type 313	page 96
	Type 314	page 96
	Type 349	page 94
	Type 350	page 94

Accessories

for Type 329
Coding set
700024 page 206


Type 329

Header, centerline 5 mm / 0.197 inches, horizontal
square contact pins 1 mm / 0.039 inches, open ends,
codable

Technical Data

 us V / A	300 / 15		
	320 V / 4 kV / 10 A		
Insulation co-ordination according to EN 60664-1			
Clearance and creepage distances	min. 4 mm		
Insulating material class	CTI 600		
Overvoltage category	III	III	II
Pollution degree	3	2	2
Rated voltage	320	800	800
Rated test voltage	4	6	4
Protection category according to IEC 529	IP00		
Solder pin dimension	1.0 x 1.0 mm		
Recommended pc board hole dia.	Ø 1.5 mm		
Solder pin length	3.45 mm		
Pole size	2 - 24		
Color	black		

Dimensions in mm 1 mm = 0.0394 in.



$L = (\text{pole size} - 1) \times \text{centerline} + 5 \text{ mm} / 0.197 \text{ inches}$

Part numbers (P/N)

(information: page 110)

Complete the part number by adding the pole size.

Type 329

centerline 5 mm / 0.197 inches

P/N 313291

	02	03	04	05	06	07	08
09	10	11	12	13	14	15	16
17	18	19	20	21	22	23	24

- Standard pole sizes
- Available on demand. Minimum order quantity 5000 pieces per item.