

DESCRIPTION: 2mm HEADER STRIP STRAIGHT

MATERIALS:


HOUSING: NYLON 6T- UL 94V-0
COLOR: BLACK
CONTACTS: COPPER ALLOY
PLATING: GOLD FLASH ENTIRE CONTACT
RoHS COMPLIANT

CURRENT RATING: 1 AMP
INSULATOR RESISTANCE: 5000 MEGOHMS MIN.
DIELECTRIC WITHSTANDING: 500V AC
OPERATING TEMP: -40°C TO +105°C
MAX PROCESSING TEMP: 260°C FOR 10 SECONDS

2763 YY 02RP2

SERIES _____
2763 = SINGLE ROW
POSITIONS _____
SINGLE - INCRMENTS OF 1
(01 TO 36)
TYPE _____
02 = RIGHT ANGLE
PLATING _____
P2 = GOLD FLASH

"L" = NO. OF PINS/ROW X .079 - .079



	THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF NorComp AND SHALL NOT BE REPRODUCED, COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OF SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.	DRAWN: PAM JENKINS		DATE: 1-27-06	
		CHECKED:		DATE:	
NorComp	SCALE:		SHEET 1 OF 1		REV 2
	DWG NO. 2763YY02RP2				

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[NorComp:](#)

[27630102RP2](#) [27630202RP2](#) [27630302RP2](#) [27630402RP2](#) [27630502RP2](#) [27630602RP2](#) [27630702RP2](#)
[27630802RP2](#) [27630902RP2](#) [27631002RP2](#) [27631202RP2](#) [27631502RP2](#) [27631602RP2](#) [27632002RP2](#)
[27632402RP2](#) [27632502RP2](#) [27632602RP2](#) [27633602RP2](#)