

Contact Us

Global Locations

Product Support



Where To Buy

Enter Zip Code:

Enter Quantity:

GO

Pin Terminals

T&B Catalog Number: 14RB-47PT
UPC Number: 78621003416
Status: Active

Description:
Insulated Vinyl Pin Terminals For Wire Range 16-14 Length .87 Diameter .075

ROHS SUBMITTAL
PACKAGE

- Features
- Provides an easy and effective way to terminate stranded wire into European/metric-style terminal blocks.

General	
Insulation Type	Insulated Vinyl
Terminal Series	RB
Material	Copper
Finish	Electro -Tin Plated
Color	Blue
Wire Range	16-14

Dimension Information	
Length (inches)	.87
Diameter D (inches)	0.075
Stock Thickness	.03

Specifications	
Temperature Rating	105°C
Voltage Rating	300V
Flammability Rating	UL 94 V-0

Tooling	
Tool Charts	Click Here
Application Tools	WT1455, ERG4001, ERG4003
Recommended Tool	ERG4001

Packaging	
Order Multiple	100
Inner Package	100
Outer Package	500
Package Type	Standard
Package Height	6.19
Package Length	3.19
Package Width	2.31
T&B Sold in UOM	Each
T&B Weight Per UOM	0.22 lbs. per 100
Alternate Package Qty	RB47PT

Application Support	
Overview	Click Here
Wire Guide Tables	Click Here

Certifications	
RoHS Compliance	Yes Generate Compliance Certificate