




PANDUIT PART NO. *	BUNDLE DIA.		A in (mm)	B in (mm)	C in (mm)	D in (mm)	E in (mm)	F in (mm)	MIN. LOOP TENSILE lbs (N)	CROSS SECTION	WEIGHT lbs/100 pcs. (g)
	MIN. in (mm)	MAX. in (mm)									
CBR3S-69	.280 (7.1)	3.0 (76.2)	.052 (1.3)	.190 (4.8)	.215 (5.5)	.280 (7.1)	.332 (8.4)	10.8 (274.3)	50 (222)	STANDARD	.39 (174.8)

NOTES:

- * 1) SEE CURRENT PRICE SHEET FOR PART NUMBER SUFFIX DESIGNATION FOR PACKAGE SIZE.
- 2) MATERIAL HAS A UL RELATIVE THERMAL INDEX RATING OF 248°F (120°C).
- 3) MATERIAL FLAMMABILITY RATING: UL94V-0.
- 4) MINIMUM LOOP TENSILE RATING AT 120°F (49°C)/20% RH.
- 5) COLOR: NATURAL--OFF WHITE.

DIMENSIONS IN PARENTHESES ARE IN METRIC UNITS

SS_27400.prt
PANDUIT CORP. TINLEY PARK, ILLINOISCBR SERIES CABLE TIE
FLAME RETARDANT SERIESUNLESS OTHERWISE SPECIFIED,
DIMENSIONAL TOLERANCES ARE:
(.X) ± .01 (.25) (.XXX) ± .020 (.51)
(.XX) ± .02 (.5) ANGLES ±UNLESS OTHERWISE SPECIFIED,
ALL DIMENSIONS ARE GIVEN
IN INCHES, THIRD ANGLE PROJECTION.DRAWN BY
JABO

MAT'L:

SCALE NONE

DATE
7/11/03FLAME RETARDANT
NYLON 6/6

DRAWING NO.

SS-27400

DWG
A
SIZE

REV	DATE	BY	CHK	DESCRIPTION
R	7-11-03	JABO		DRAWING RELEASED

ECN	R	CUST	SUP
27400	R		