



CK17M

Contact surface probe, 45 degree angle



Copyright © 2007 Test Products International, Inc.

Application

Contact temperatures on flat and uneven high temperature surfaces

Range°F°C

-40° to 950°F
-40° to 510°C

Probe tip

32

Dimensions

Stem Length: 4" (102mm)
w/45° bend
Diameter: 0.3" (7.5mm)
Lead Length: 39.4" (1M)

Insulation Material

Polyurethane