



	1	2	3	4	5	6	7	
--	---	---	---	---	---	---	---	--



Cable White print
 AWM STYLE 2725 80°C 30V VW-1 28AWG/1P 24AWG/2C
 ---C AWM I/II A 80°C 30V FT1 USB CABLE

WSW P/N	Jacket color	Length(mm)
AK67321-0.5	Black	500±15
AK67321-1	Black	1000±20
AK67321-2	Black	2000±20
AK67321-3	Black	3000±30
AK67321-5	Black	5000±50

- Electrical test:
1. 100% short, open, miss wire test
 2. Conduct resistance: 2 Ohm max.
 3. Insulator resistance: 10Mohm min.
 4. Dielectric test: DC 300V



PIN ASSIGNMENT			
P1			P2
1	Red	1	
2	White	2	
3	Green	3	
4+5	Black	4	
Shell	Drain+Braid	Shell	

⑥	PE Bag	1	Clear Print black "MADE IN CHINA"+ "1PC"
⑤	TIE	1	Black
④	Out Jacket	NA	Black PVC-45P
③	CONN	1	Micro USB 5P A Male Shell:Nickel Pin:G/F Insulator color: Black solder type
②	CONN	1	USB 2.0 A Male Shell:Nickel Pin:G/F Insulator color: White solder type
①	Cable	1	USB 2.0 UL2725 (28#*1P+AL)+28#2C+AEB Black OD:3.5mm
NO.	NAME.	Q'TY	SPECIFICATION

Scale	Free					Customer-No.	
TOLERANCE						Drawn	21.03.2016
						Approved	21.03.2016
DIM	TOL						
Angle	TOL	①	Drawn			Any	21.03.2016



Drawing-No. ASS 7590 CA rev00
 Replace Sheet

	1	2	3	4	5	6	7	
--	---	---	---	---	---	---	---	--

RoHS compliant
 Unit: mm