

Part Number **PAG.M1.4GL.AC52J**



Size/Series P / 1P

[Request a quote](#)

MECHANICAL DETAILS

Shell Style/Model PA*: Straight plug with cable collet
Keying 1 key (alpha=0; Plug: male contact; Receptacle: female contact)
Housing Material PSU (Polysulfone), gray
Cable Fixing C52: 4 - 5.2 mm
Variant J : Yellow collet nut

	A	L
mm.	14	45
in.	0.55	1.77



PERFORMANCE DETAILS

Insert Configuration 1P.M14 : 14 Low Voltage
Test voltage (kV rms) 0.6
Contact-contact:
Air clearance min. (mm) or Creepage distance min. (mm): 0.5
Rated current (A): 2

OTHER CHARACTERISTICS

F ret (min): 50 N
F ret (max): 150 N
IP Rating 50
Catalog

[Download 3D draw](#)[Copyright](#) [Privacy policy](#) [Product safety](#)