




FCIconnect.com

Copyright FCI

PRODUCT NUMBER

SEE TABLE



mat'l. code				surface  ISO 1302			tolerance  ISO 406  ISO 1101	projection 	product family CARD CONN			
ltr	ecn no	dr	date	tolerances unless otherwise specified				INCH/MM	title			
X	REVISED	EBY	2/14/86	angles	linear	.XX±.01/.X±.3			1X.150 HORIZ. CARD CONN.			
Y	V61618	MDF	10/31/96			.XXX±.0.005/.XX±.13		HT NYLON				
AA	V70992	JM	10/12/97			0'±2'	.XXXX±.0020/.XXX±.051	scale 4:1				
AB	V02523	AZ	10/23/00	dr	M.CLOUSER	10/2/85		dwg no		sheet 1 of 6	size	
AC	M05-0199	ERE	09/15/05	enr	H.SUNDY	10/31/96		65059			A3	
AD	M06-0210	MHT	6/03/06	chr	H.SUNDY	10/31/96						
				appd	H.SUNDY	10/31/96						
sheet index		revision sheet		AD	AD	AD	AD	AD	AD			
				1	2	3	4	5	6			


form: A3




FCIconnect.com

Copyright FCI

PRODUCT NUMBER
SEE TABLE



RECOMMENDED MOUNTING HOLE PATTERN
SCALE 4/1



MATING PIN PATTERN
SCALE 4/1

- ALL MATING .025/0.64 SQ. PINS ON TRUE CENTER OF BASIC DIMENSIONS WITHIN .015/0.38 DIA.
- SUGGESTED MATING PIN LENGTH .350±.020/8.89±0.51.

NOTES:

- HOUSING MAT'L:
FILLED HIGH TEMPERATURE NYLON
COLOR: BLACK
- TERMINAL MATERIAL:
BODY: BRASS, .010/0.250 THK
SPRING: BE-CU, HEAT TREATED. SEE TABLE FOR THICKNESS
PLATING:
40u"/1.02u Au IN CONTACT AREA (STANDARD PLATING)
(EXCEPTIONS NOTED IN TABLE)
- ADD "LF" SUFFIX AT THE END OF PART NUMBER FOR LEAD FREE OPTION.
- THESE PRODUCTS MEET EUROPEAN UNION DIRECTIVES AND OTHER COUNTRY REGULATIONS AS DESCRIBED IN GS-22-008.
- THIS PART WILL WITHSTAND EXPOSURE TO 260°C PEAK TEMPERATURE FOR 20 SECONDS IN WAVE SOLDER, INFRA-RED OR VAPOR PHASE SOLDER PROCESS.
- "THIS PRODUCT HAS 100% TIN PLATING IN THE INTERFACE AND HAS NOT BEEN TESTED FOR WHISKER GROWTH IN ALL INTERCONNECT ENVIRONMENTS."
- MARKING FCI PART NUMBER & DATE CODE LEGIBLE ON TUBE LABEL.

mat'l. code				surface ISO 1302 ✓	tolerance ISO 406 ISO 1101	projection INCH/MM	product family CARD CONN
ltr	ecn	no	dr	date	tolerances unless otherwise specified	INCH/MM scale 4:1 FCI	title
AD					angles linear .XX±.01/.X±.3 .XXX±.0.005/.XX±.13 .XXXX±.0020/.XXX±.051		1X.150 HORIZ. CARD CONN. HT NYLON
					dr M.CLOUSER 10/2/85		dwg no sheet 2 of 6 size
					enr H.SUNDY 10/31/96		65059 A3
					chr H.SUNDY 10/31/96		type Product Customer Drawing
					appd H.SUNDY 10/31/96		
sheet index	revision sheet						

form: A3



FCIconnect.com

Copyright FCI

PRODUCT NO.	NO OF POS	DIM "L"	DIM "M"	HOUSING MATERIAL	SPRING THICKNESS	BODY PLATING THICKNESS	CUSTOMER RESTRICTED	LEAD FREE OPTION
65059-001	1 X 5	.600/15.24	.740/18.80	HT NYLON	.0035/0.089	40u"/1.02u Au		NOTE 3, 4
-002	1 X 6	.750/19.05	.890/22.61					
-003	1 X 7	.900/22.86	1.040/26.42					
-004	1 X 8	1.050/26.67	1.190/30.23					
-005	1 X 9	1.200/30.48	1.340/34.04					
-006	1 X 10	1.350/34.29	1.490/37.85					
-007	1 X 11	1.500/38.10	1.640/41.66					
-008	1 X 12	1.650/41.91	1.790/45.47					
-009	1 X 13	1.800/45.72	1.940/49.28					
-010	1 X 14	1.950/49.53	2.090/53.09					
-011	1 X 15	2.100/53.34	2.240/56.90					
-012	1 X 16	2.250/57.15	2.390/60.71					
-013	1 X 17	2.400/60.96	2.540/64.52					
-014	1 X 18	2.550/64.77	2.690/68.33					
-015	1 X 19	2.700/68.58	2.840/72.14					
-016	1 X 20	2.850/72.39	2.990/75.95					
-017	1 X 21	3.000/76.20	3.140/79.76					
-018	1 X 22	3.150/80.01	3.290/83.57					
-019	1 X 23	3.300/83.82	3.440/87.38					
-020	1 X 24	3.450/87.63	3.590/91.19					
-021	1 X 25	3.600/91.44	3.740/95.00					
-022	1 X 26	3.750/95.25	3.890/98.81					
-023	1 X 27	3.900/99.06	4.040/102.62					
-024	1 X 28	4.050/102.87	4.190/106.43					
65059-025	1 X 29	4.200/106.68	4.340/110.24	HT NYLON	.0035/0.089	40u"/1.02u Au		NOTE 3, 4

mat'l. code				surface ISO 1302 ☒		tolerance ISO 406 ISO 1101	 INCH/MM scale 4:1 	product family CARD CONN	
ltr	ecn no	dr	date	tolerances unless otherwise specified				title 1X.150 HORIZ. CARD CONN. HT NYLON	
AD				angles	linear	.XX±.01/.X±.3 .XXX±.0.005/.XX±.13 .XXXX±.0020/.XXX±.051		dwg no 65059	
				0'±2'				sheet 3 of 6 size A3	
				dr	M.CLOUSER	10/2/85		type Product Customer Drawing	
				enr	H.SUNDY	10/31/96			
				chr	H.SUNDY	10/31/96			
				appd	H.SUNDY	10/31/96			
sheet index	revision sheet								



FCIconnect.com

Copyright FCI

form: A3

PRODUCT NO.	NO OF POS	DIM "L"	DIM "M"	HOUSING MATERIAL	SPRING THICKNESS	BODY PLATING THICKNESS	CUSTOMER RESTRICTED	LEAD FREE OPTION
65059-026	1 X 30	4.350/110.49	4.490/114.05	HT NYLON	.0035/0.089	40u"/1.02u Au		NOTE 3, 4
-027	1 X 12	1.650/41.91	1.790/45.47				RESTRICTED	
-028	1 X 26	3.750/95.25	3.890/98.81				RESTRICTED	
-029	1 X 1	.000/0.00	.140/3.56					
-030	1 X 2	.150/3.81	.290/7.37					
-031	1 X 3	.300/7.62	.440/11.81					
-032	1 X 4	.450/11.43	.590/14.99			40u"/1.02u Au		
-033	1 X 8	1.050/26.67	1.190/30.23			100u"/2.54u TIN LEAD	RESTRICTED	
-034	1 X 30	4.350/110.49	4.490/114.05			100u"/2.54u TIN LEAD	RESTRICTED	
-035	1 X 16	2.250/57.15	2.390/60.71			40u"/1.02u Au	RESTRICTED	
-036	1 X 24	3.450/87.63	3.590/91.19			50u"/1.27u Au		
-037	1 X 28	4.050/102.87	4.190/106.43			50u"/1.27u Au		
-038	1 X 13	1.800/45.72	1.940/49.28			40u"/1.02u Au		
-039	1 X 15	2.100/53.34	2.240/56.90			40u"/1.02u Au		
-040	1 X 27	3.900/99.06	4.040/102.61			40u"/1.02u Au		
-041	1 X 18	2.550/64.77	2.690/68.33		.0035/0.089	100u"/2.54u Au	RESTRICTED	
-042	1 X 22	3.150/80.01	3.290/83.57		.0048/0.122	40u"/1.02u Au	RESTRICTED	
-043	1 X 5	.600/15.24	.740/18.80		.0035/0.089	40u"/1.02u Au	RESTRICTED	
65059-044	1 X 7	.900/22.86	1.040/26.42	HT NYLON	.0035/0.089	40u"/1.02u Au	RESTRICTED	NOTE 3, 4

-OBS.

mat'l. code				surface ☒ ISO 1302		tolerance ☒ ISO 406 ☒ ISO 1101	 INCH/MM scale 4:1 	product family CARD CONN		
ltr	ecn no	dr	date	tolerances unless otherwise specified				title		
AD				angles	linear	.XX±.01/.X±.3 .XXX±.0.005/.XX±.13 .XXXX±.0020/.XXX±.051		1X.150 HORIZ. CARD CONN. HT NYLON		
				0'±2'				dwg no		
				dr	M.CLOUSER	10/2/85		sheet 4 of 6		size
				enr	H.SUNDY	10/31/96		65059		A3
				chr	H.SUNDY	10/31/96				
				appd	H.SUNDY	10/31/96		type		Product Customer Drawing
sheet index		revision sheet								



FCIconnect.com

Copyright FCI

D

PRODUCT NO.	NO OF POS	DIM "L"	DIM "M"	HOUSING MATERIAL	SPRING THICKNESS	BODY PLATING THICKNESS	CUSTOMER RESTRICTED	LEAD FREE OPTION	
65059-201	1 X 1	.000/0.00	.140/3.56	HT-NYLON	.0035/0.089	100u"/2.54u TIN LEAD			OBS.
-202	1 X 2	.150/3.81	.290/7.37	HT NYLON	.0035/0.089	100u"/2.54u TIN LEAD		NOTE 3, 4	
-203	1 X 3	.300/7.62	.440/11.18						
-204	1 X 4	.450/11.43	.590/14.99						
-205	1 X 5	.600/15.24	.740/18.80						
-206	1 X 6	.750/19.05	.890/22.61						
-207	1 X 7	.900/22.86	1.040/26.42						
-208	1 X 8	1.050/26.67	1.190/30.23						
-209	1 X 9	1.200/30.48	1.340/34.04						
-210	1 X 10	1.350/34.29	1.490/37.85						
-211	1 X 11	1.500/38.10	1.640/41.66						
-212	1 X 12	1.650/41.91	1.790/45.47						
-213	1 X 13	1.800/45.72	1.940/49.28						
-214	1 X 14	1.950/49.53	2.090/53.09						
-215	1 X 15	2.100/53.34	2.240/56.90						
-216	1 X 16	2.250/57.15	2.390/60.71						
-217	1 X 17	2.400/60.96	2.540/64.52						
-218	1 X 18	2.550/64.77	2.690/68.33						
-219	1 X 19	2.700/68.58	2.840/72.14						
-220	1 X 20	2.850/72.39	2.990/75.95						
-221	1 X 21	3.000/76.20	3.140/79.76						
-222	1 X 22	3.150/80.01	3.290/83.57						
-223	1 X 23	3.300/83.82	3.440/87.38						
-224	1 X 24	3.450/87.63	3.590/91.19						
65059-225	1 X 25	3.600/91.44	3.740/95.00	HT NYLON	.0035/0.089	100u"/2.54u TIN LEAD		NOTE 3, 4	

mat'l. code				surface ISO 1302 ☒ ISO 406 ISO 1101		tolerance ISO 406 ISO 1101		projection 		product family CARD CONN	
ltr	ecn	no	dr	date	tolerances unless otherwise specified					title	
AD					angles	linear	.XX±.01/.X±.3 .XXX±.0.005/.XX±.13 .XXXX±.0020/.XXX±.051	INCH/MM		1X.150 HORIZ. CARD CONN. HT NYLON	
					0°±2°			scale 4:1		dwg no	
					dr	M.CLOUSER	10/2/85			sheet 5 of 6 size	
					enrg	H.SUNDY	10/31/96			65059 A3	
					chr	H.SUNDY	10/31/96			type Product Customer Drawing	
					appd	H.SUNDY	10/31/96				
sheet index	revision										
	sheet										

PRODUCT NO.	NO OF POS	DIM "L"	DIM "M"	HOUSING MATERIAL	SPRING THICKNESS	BODY PLATING THICKNESS	CUSTOMER RESTRICTED	LEAD FREE OPTION
65059-226	1 X 26	3.750/95.25	3.890/98.81	HT NYLON	.0035/0.089	100u"/2.54u TIN LEAD		NOTE 3, 4
-227	1 X 27	3.900/99.06	4.040/102.62					
-228	1 X 28	4.050/102.87	4.190/106.43					
-229	1 X 29	4.200/106.68	4.340/110.24					
-230	1 X 30	4.350/110.49	4.490/114.05		.0035/0.089			
65059-231	1 X 31	3.150/80.01	3.290/83.57	HT NYLON	.0048/0.122	100u"/2.54u TIN LEAD	RESTRICTED	NOTE 3, 4

mat'l. code				surface ISO 1302 ☒		tolerance ISO 406 ISO 1101		projection 		product family CARD CONN				
ltr	ecn	no	dr	date	tolerances unless otherwise specified					title				
AD					angles	linear	.XX±.01/.X±.3			1X.150 HORIZ. CARD CONN.				
					0'±2'		.XXX±.0.005/.XX±.13			HT NYLON				
							.XXXX±.0020/.XXX±.051			scale 4:1				
					dr	M.CLOUSER	10/2/85				dwg no		sheet 6 of 6	size
					enr	H.SUNDY	10/31/96				65059		A3	
					chr	H.SUNDY	10/31/96							
					appd	H.SUNDY	10/31/96							
sheet index		revision sheet												