




W54-XA1A99C10-15 Product Details



W54-XA1A99C10-15

TE Internal Number: 5-1423674-2



Thermal Circuit Breakers

Always EU RoHS compliant but not ELV Compliant
(Statement of Compliance)

Product Highlights:

- Circuit Breaker
- W54 Series
- 1 Poles
- Actuator Style = Push to Reset
- Current Rating = 15 A

Documentation & Additional Information	
Product Drawings: • None Available Catalog Pages/Data Sheets: • W54 Push To Reset Only Thermal Circuit Breaker (PDF, English) Product Specifications: • None Available Application Specifications: • None Available Instruction Sheets: • None Available CAD Files: • None Available	Additional Information: • Product Line Information Additional Product Images: • Schematic Related Products: • Tooling

Product Features (Please use the Product Drawing for all design activity)	
Product Type Features: • Product Type = Circuit Breaker • Series = W54 • Actuator Style = Push to Reset • Termination Type = 6.35 [.250] Straight Quick Connect Tab Mechanical Attachment: • Mounting Options = None • Mounting Bushing = 9.8 mm x 12.6 mm Long, Metal Electrical Characteristics: • Current Rating (A) = 15 • Operating Voltage, Max. = 250 VAC • Interrupt Capacity = 1,000 A @ 250 VAC Body Features: • Button Color = White, Plain, No Rate Marking	Contact Features: • Number of Poles = 1 • Trip Time at 200% = 5 to 40 Seconds Configuration Features: • Circuit Function = Series Trip Industry Standards: • RoHS/ELV Compliance = RoHS/Not ELV Compliant • Lead Free Solder Processes = Not relevant for lead free process • RoHS/ELV Compliance History = Always was RoHS not ELV compliant Packaging Features: • Mounting Hardware Packaging = No Mounting Hardware Other: • Brand = Potter & Brumfield