

Stinger® Rechargeable Flashlight

FL 1 STANDARD	
	90 LUMENS
	1h 15min
	210m
	11,000cd
	
	2m

Product is tested per ANSI/NEMA FL-1 2009 standard



Case Material: Machined aluminum housing that is anodized against corrosion inside and out and an unbreakable polycarbonate lens with scratch-resistant coating

Dimensions/ Length: 7.38 in. (18.7 cm) Major Diameter: 1.60 in. (4.06 cm); Body Diameter: 1.08 in. (2.74 cm)
Weight: 10 ounces (284 grams)*

Light Source: Xenon gas-filled bi-pin bulb with 30-hour life, with a spare stored in the end cap, variable spot-to-flood beam

On/Off: Push-button head switch. Momentary or constant on

Battery: 3-Cell, 3.6-Volt Nickel-cadmium sub-C battery is rechargeable up to 1000 times
 3-cell, 3.6 Volt Ni-MH sub-C battery, rechargeable up to 1000 times offered in 230V AC and 12V DC European systems

Charging: Ten hours to fully recharge, 2.5-hour fast charger or PiggyBack® charger model available

- Features:**
- IPX4 rated design; water resistant
 - LED charge-continuity indicator, compact
 - Serialized for positive identification
 - 2 meter impact resistance tested.
 - Snap-in charger holder that mounts in any position

Approvals:**  UL Listed Class I, Div. 2, Groups A,B,C,D T1; Class II, Div. 2, Groups F,G T3
 Most models meet applicable European Community Directives.

Warranty: Streamlight's Limited Lifetime Warranty warrants this product to be free of defect for a lifetime of use. We will repair, replace or refund the purchase price, at our option, of any Streamlight product that does not work as a result of a manufacturing defect for as long as you own it. This limited lifetime warranty excludes abuse, batteries, bulbs, chargers, switches, electronics and normal wear and tear. Rechargeable batteries, chargers, switches and electronics have a two (2) year warranty with proof of purchase.

*With battery (included in purchase).

**See product for specific ratings.

Item	UPC	Item
Steady Charge		
Stinger with 230V AC/DC	080926-75214-6	75214
Stinger with 120V AC/DC	080926-75014-2	75014
Stinger with 230V AC	080926-75201-6	75201
Stinger with 120V AC	080926-75001-2	75001
Steady Charge PiggyBack		
Stinger with 120V AC/DC	080926-75300-6	75300
(W/OUT CHARGER)		
Stinger	080926-75000-5	75000
See reverse for additional part numbers		

See reverse for 230V NiMH configurations





Item Description - NiMH Configurations	UPC	Part #
Stinger 230V AC/DC - 2 Holders NiMH Battery	080926-75163-7	75163
Stinger 230V AC NiMH Battery	080926-75162-0	75162
Stinger 12V DC NiMH Battery	080926-75068-5	75068
Stinger 230V AC Fast Charge NiMH Battery	080926-75164-4	75164
Stinger 230V AC/DC Fast Charge NiMH Battery	080926-75165-1	75165
Stinger 12V DC Fast Charge NiMH Battery	080926-75069-2	75069
Stinger (WITHOUT CHARGER) NiMH Battery	080926-75161-3	75161

Item	UPC	Part #
DC2 direct wire charge cord	080926-22050-8	22050
DC1 Charge Cord	080926-22051-5	22051
120V AC charge cord	080926-22311-0	22311
100V AC charge cord	080926-22666-1	22666
230V AC charge cord	080926-22664-7	22664
240V AC charge cord	080926-22241-0	22241
Charger Holder Stinger (10 Hour)**	080926-75100-2	75100
Charger Holder Fast Charge (2.5 hour)**	080926-75103-3	75103
5 Unit Bank Charger, 120V	080926-75400-3	75400
5 Unit Bank Fast Charger, 120V	080926-75401-6	75401
5 Unit Bank Charger, 230V	080926-75600-7	75600
5 Unit Bank Fast Charger, 230V	080926-75601-4	75601
5 Unit Bank Charger, 100V	080926-75700-4	75700
5 unit bank charger 100V	080926-75701-1	75701
PiggyBack® Charger Holder - Steady Charger & Battery	080926-75275-7	75275
PiggyBack® Charger Holder Fast Charger & Battery	080926-75276-4	75276
Flip Lens IR	080926-75027-2	75027
Flip Lens Red	080926-75115-6	75115
Flip Lens Blue	080926-75116-3	75116
Flip Lens Green	080926-75117-0	75117
Lens replacement kit	080926-75160-6	75160
HP Upgrade Kit (Converts Stinger to Stinger HP)	080926-78004-0	78004
Switch Module ** Special tool required for installation	080926-75140-8	75140
NiCd Battery Stick	080926-75175-0	75175
NiMH Battery Stick	080926-75375-4	75375
Bulb	080926-75914-5	75914
Lens/Reflector Assembly	080926-75956-5	75956
Safety Wand Blue	080926-75902-2	75902
Safety Wand Red	080926-75903-9	75903
Safety Wand Yellow	080926-75904-6	75904
Safety Wand White	080926-75908-4	75908
Safety Wand Glow in the Dark	080926-75913-8	75913
Holster, Stinger, Stinger XT, PolyStinger (Deluxe Nylon)	080926-75909-1	75909
Ring Holder	080926-75906-0	75906
Holster (Nylon)	080926-76090-5	76090
Loop holster	080926-75928-8	75928
Leather holster: Plain - Stinger/Stinger XT/Poly/Stinger	080926-75135-4	75135
Leather holster: Basket Weave - Stinger/Stinger XT/Poly/Stinger	080926-75136-1	75136