

Sales Outline Drawing

Revision

A

Specifications:

Voice Coil Impedance (Ω)	$8 \pm 15\%$ at 800 Hz / 1.0 V
Rated Input (W)	0.25
Max. Input (W)	0.30
Lowest Resonance Freq Fo (Hz)	$1600 \pm 20\%$
Frequency Range (Hz)	Fo ~ 9000
Output S.P.L. (dB)	75 ± 3 at 1W 1M .8k, 1k, 1.2k, 1.5kHz
Magnet Size (mm)	$\varnothing 10.5 * 1.0$
Magnet	Ferrite
Core Material Mylar	Transparent Radial
Frame Material	Plastic
Options	For other options contact factory

Dimensions: (units: mm)

ROHS Compliant

