



## GX15B

### Shielded air probe



Copyright © 2007 Test Products International, Inc.

#### Application

Air

#### Range°F°C

-40° to 300°F  
-40° to 150°C

#### Probe tip

44

#### Dimensions

Stem Length: 3.15" (80mm)  
Diameter: .13" (3.2mm)  
Lead Length: 15.7" (0.4M)

#### Insulation Material

PVC