




IDC POKE-IN WIRE CONNECTORS

Available In Surface Mount And Thru-Hole For Wire-To-Board Connectivity

IDC POKE-IN WIRE CONNECTOR

TE Connectivity's (TE) IDC Poke-In Wire connector series are insulation displacement (IDC) connectors that are available in surface mount and thru-hole for wire-to-board connectivity. These connectors are designed for quick, tool-less termination of discrete solid and stranded wire leads to metal clad boards used in LED applications and FR4 boards used in thru-hole non-LED lighting applications. These connectors use TE Connectivity (TE) reliable insulation displacement technology to prove a robust, stable electrical and mechanical power connection to single or multiple printed circuit boards.

ELECTRICAL

- Current rating: 8A with 18 AWG
- Voltage rating: 400 VAC / 400 VDC
- Dielectric strength: 1500 VAC

MECHANICAL

- Operating Temperature: -40°C to 105°C
- Wire retention: 5 lbs. max

MATERIALS

- Housing: PA UL94 V-0
- Contact: Tin over nickel plated
- Copper Alloy

SPECIFICATIONS

- Applications Specification: [114-13266](#)
- Product Specification: [108-2404](#)
- UL Approvals: 1977

COLORS

- 18 AWG - Yellow
- 20 AWG - Blue
- 22 AWG - Green
- 24 AWG - Red

BENEFITS

- Insulation displacement helps eliminate the need to pre-strip wire insulation prior to "tool-less" termination
- Integral cover provides wire entry location and when fully seated wire leads are secured in dual IDC slots help ensure electrical connections
- Integral cover provides a robust, mechanical strain relieved connection in high vibration applications
- Wire placement viewing window and wire gauge color coded housings assist in error resistant assembly
- Closed end versions are used in single discrete wire lead electrical connections
- Feed thru versions are used in multiple board "daisy chaining" electrical connections

APPLICATIONS

- LED lighting
- HVAC controls
- Fire and security controls
- Household appliances
- Power tools

IDC POKE-IN WIRE CONNECTOR

CLOSED END IDC SSL CONNECTORS (SMT)

Part Number	Position	Wire Size	Dim "D"	Color
2106003-1*	1	18 AWG	5.70 [.224]	YELLOW
2106003-2*	2	18 AWG	9.70 [.382]	YELLOW
2106003-3*	3	18 AWG	13.70 [.539]	YELLOW
2106003-4	4	18 AWG	17.70 [.697]	YELLOW
1-2106003-1*	1	20 AWG	5.70 [.224]	BLUE
1-2106003-2*	2	20 AWG	9.70 [.382]	BLUE
1-2106003-3*	3	20 AWG	13.70 [.539]	BLUE
1-2106003-4	4	20 AWG	17.70 [.697]	BLUE
2-2106003-1	1	22 AWG	5.70 [.224]	GREEN
2-2106003-2	2	22 AWG	9.70 [.382]	GREEN
2-2106003-3	3	22 AWG	13.70 [.539]	GREEN
2-2106003-4	4	22 AWG	17.70 [.697]	GREEN
3-2106003-1	1	24 AWG	5.70 [.224]	RED
3-2106003-2	2	24 AWG	9.70 [.382]	RED
3-2106003-3	3	24 AWG	13.70 [.539]	RED
3-2106003-4	4	24 AWG	17.70 [.697]	RED



FEED THRU IDC SSL CONNECTORS (SMT)

Part Number	Position	Wire Size	Dim "D"	Color
2106431-1*	1	18 AWG	5.70 [.224]	YELLOW
2106431-2*	2	18 AWG	9.70 [.382]	YELLOW
2106431-3*	3	18 AWG	13.70 [.539]	YELLOW
2106431-4	4	18 AWG	17.70 [.697]	YELLOW
1-2106431-1*	1	20 AWG	5.70 [.224]	BLUE
1-2106431-2*	2	20 AWG	9.70 [.382]	BLUE
1-2106431-3*	3	20 AWG	13.70 [.539]	BLUE
1-2106431-4	4	20 AWG	17.70 [.697]	BLUE
2-2106431-1*	1	22 AWG	5.70 [.224]	GREEN
2-2106431-2*	2	22 AWG	9.70 [.382]	GREEN
2-2106431-3	3	22 AWG	13.70 [.539]	GREEN
2-2106431-4	4	22 AWG	17.70 [.697]	GREEN
3-2106431-1	1	24 AWG	5.70 [.224]	RED
3-2106431-2	2	24 AWG	9.70 [.382]	RED
3-2106431-3	3	24 AWG	13.70 [.539]	RED
3-2106431-4	4	24 AWG	17.70 [.697]	RED

*Preferred part numbers

IDC POKE-IN WIRE CONNECTOR

CLOSED END IDC SSL CONNECTORS (THRU-HOLE)

Part Number	Position	Wire Size	Dim "D"	Color
2106489-1	1	18 AWG	5.70 [.224]	YELLOW
2106489-2	2	18 AWG	9.70 [.382]	YELLOW
2106489-3	3	18 AWG	13.70 [.539]	YELLOW
2106489-4	4	18 AWG	17.70 [.697]	YELLOW
1-2106489-1	1	20 AWG	5.70 [.224]	BLUE
1-2106489-2	2	20 AWG	9.70 [.382]	BLUE
1-2106489-3	3	20 AWG	13.70 [.539]	BLUE
1-2106489-4	4	20 AWG	17.70 [.697]	BLUE
2-2106489-1	1	22 AWG	5.70 [.224]	GREEN
2-2106489-2	2	22 AWG	9.70 [.382]	GREEN
2-2106489-3	3	22 AWG	13.70 [.539]	GREEN
2-2106489-4	4	22 AWG	17.70 [.697]	GREEN
3-2106489-1	1	24 AWG	5.70 [.224]	RED
3-2106489-2	2	24 AWG	9.70 [.382]	RED
3-2106489-3	3	24 AWG	13.70 [.539]	RED
3-2106489-4	4	24 AWG	17.70 [.697]	RED

CLOSED END IDC SSL CONNECTORS (THRU-HOLE)

Part Number	Position	Wire Size	Dim "D"	Color
2106751-1	1	18 AWG	5.70 [.224]	YELLOW
2106751-2	2	18 AWG	9.70 [.382]	YELLOW
2106751-3	3	18 AWG	13.70 [.539]	YELLOW
2106751-4	4	18 AWG	17.70 [.697]	YELLOW
1-2106751-1	1	20 AWG	5.70 [.224]	BLUE
1-2106751-2	2	20 AWG	9.70 [.382]	BLUE
1-2106751-3	3	20 AWG	13.70 [.539]	BLUE
1-2106751-4	4	20 AWG	17.70 [.697]	BLUE
2-2106751-1	1	22 AWG	5.70 [.224]	GREEN
2-2106751-2	2	22 AWG	9.70 [.382]	GREEN
2-2106751-3	3	22 AWG	13.70 [.539]	GREEN
2-2106751-4	4	22 AWG	17.70 [.697]	GREEN
3-2106751-1	1	24 AWG	5.70 [.224]	RED
3-2106751-2	2	24 AWG	9.70 [.382]	RED
3-2106751-3	3	24 AWG	13.70 [.539]	RED
3-2106751-4	4	24 AWG	17.70 [.697]	RED

*Preferred part numbers

View Products

Contact Our Product Team

We make it easy to connect with our experts and are ready to provide the support you need.

Visit te.com/support to chat with a Product Information Specialist.

te.com/poke-in-wire-connectors

TE, TE Connectivity and TE connectivity (logo) are trademarks owned or licensed by the TE Connectivity plc family of companies. Other product names, logos, and company names mentioned herein may be trademarks of their respective owners.

While TE has made every reasonable effort to ensure the accuracy of the information in this document, TE does not guarantee that it is error-free, nor does TE make any other representation, warranty or guarantee that the information is accurate, correct, reliable or current. TE reserves the right to make any changes to the information contained herein without prior notice. TE Connectivity's obligations shall only be as set forth in TE Connectivity's Standard Terms and Conditions of Sale for this product and in no case will TE Connectivity be liable for any incidental, indirect, or consequential damages arising out of the sale, resale, use, or misapplication of the product. TE expressly disclaims any implied warranties with respect to the information contained herein, including, but not limited to, implied warranties of merchantability or fitness for a particular purpose. Dimensions, specifications and/or information contained herein are for reference purposes only and are subject to change without notice. Consult TE for the latest dimensions, specifications and/or information. Users of TE Connectivity products must make their own assessment as to whether the respective product is suitable for the respective desired application.

©2025 TE Connectivity. All Rights Reserved.

05-25